

Bar hangers and brackets



BCBK-01



BCBK-20



6010DW-25 / 6010ADW-25



6011DW-25 / 6011ADW-25



CI1060



Cat. No.	Description
Bar hangers	
BCBK-01	Adjustable hanger for wood stud. Length: 15.5 in. Height: 2.5 in.
BCBK-20	Adjustable hanger for octagonal boxes for furring channel. Width: 4 1/2 in. x Height: 1 3/8 in. x Length: 21 1/8 in.
CI1060	Length: 16 in. Grooved for box ears



Cat. No.	Description	Maximum Load Capacity	Length
Adjustable bar hangers for 3/8 in., 1/2 in. and 5/8 in. drywall and plaster			
6010DW-25	Score marks for drywall and plaster depths. Packaged complete with stud.	50 lb (22.7 kg)	10 1/2 in. to 18 in.
6010ADW-25	Score marks for drywall and plaster depths. Packaged complete with stud.	50 lb (22.7 kg)	14 1/2 in. to 25 in.
6011DW-25	Score marks for drywall and plaster depths. Packaged complete with fastener.	50 lb (22.7 kg)	10 1/2 in. to 18 in.
6011ADW-25	Score marks for drywall and plaster depths. Packaged complete with fastener.	50 lb (22.7 kg)	14 1/2 in. to 25 in.

Note: These products replace Iberville BC1041 and BC1042 bar hangers.

Steel City Bar hangers and brackets

Extra heavy-duty new work bar hanger

Ceiling fan and light fixture bar hanger

This innovative extruded-aluminum bar hanger was designed for strength. It is cULus Listed for up to 70 lb for fan support and 200 lb for fixture support.

Features and benefits

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- Screwed-on end plates are consistently strong and avoid unsightly welds
- End plates feature temporary fixing spikes for hands-free installation
- Expandable for joints spaced from 14.5 in. to 24 in.



Cat. No.	Description	Volume (Cu. in.)
54151CFB-NW	New work bar hanger with 4 in. octagonal 1 1/2 in. deep box with NMD90 cable clamps (wood screws included). Maximum load capacity: Fan 70 lb and fixture 200 lb	15.8

Steel City Bar hangers and brackets

Extra heavy-duty rework bar hanger

Ceiling fan and light fixture bar hanger

Exhaustive research and development has resulted in an innovative ceiling fan support boxes that give ABB the competitive advantage. Ceiling fan and fixture installation is faster, easier and safer with Steel City ceiling fan support boxes.

Features and benefits

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- cULus Listed up to 70 lb for fan and 200 lb for light fixture
- Square end plates keep the bar parrallel with sheetrock
- Expandable for joints spaced from 14.5 in. to 24 in.



Cat. No.	Description	Volume (Cu. in.)
54151CFB-OW	Rework bar hanger with 4 in. octagonal 1½ in. deep box with NMD90 cable clamps. Maximum load capacity: Fan 70 lb and fixture 200 lb	15.8