Steel stud boxes

Device boxes



CI3102-LSSAX



CI3102-SSX



CI2104-LSSAX

CI2104-LSSA-2X

CI2104-LSSX



CI2104-LSS1X-1

CI2104-LSS2X-1



CI2104-LSS3X-1

CI-2104-LSS-2X

CI-2104-LSS-3X

CISSX-6

Cat. No.	Volume (Cu. in.)	Width (in.)	Features Clamps	Knockouts ½ in. ends	Knockouts ½ in. bottom	Knockouts ¾ in. ends	Pryouts ends
Device boxes – 2 in. deep – gangable – 3 in. high							
CI3102-LSSAX	12.0	2	BX/Loomex	–	–	–	4
CI3102-SSX	12.0	2	–	2	–	–	–
Device boxes – 2½ in. deep – pre-ganged – 3 in. high							
CI2104-LSSAX	12.5	2	BX/Loomex	–	–	–	4
CI2104-LSSA-2X	25.0	3¾	BX/Loomex	–	–	–	8
CI2104-LSSA-3X	37.5	5½	BX/Loomex	–	–	–	12
CI2104-LSSA-4X	50.0	7⅜	BX/Loomex	–	–	–	16
CI2104-LSSX	12.5	2	Loomex/BX	–	–	–	4
CI2104-LSS1X-1	12.5	2	Loomex/BX	–	–	–	4
CI2104-LSS2X-1	25.0	3¾	Loomex/BX	–	–	–	8
CI2104-LSS3X-1	37.5	5½	Loomex/BX	–	–	–	12
CI-2104-LSS-2X	25.0	3¾	Loomex/BX	–	–	–	8
CI-2104-LSS-3X	37.5	5½	Loomex/BX	–	–	–	12
CI2104-LSS-4X	50.0	7⅜	Loomex/BX	–	–	–	16

Cat. No.	Description
Support brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel stud boxes

Device boxes

CI3104-KSSX



CI3104-KSSX-5/8

CI3104-KSSX-NG*



BC3104-KSS1X-1



BC3104-LSSAX

BC3104-LSSX



BC3104-LSSAX-NG*

CI3104-LSS1X-1



CI3104-LSSA1X-1



CI1504-LSSAX



CI3004-LSSAX-1

CI3004-LSSX-1

CISSX-6

* Heavy-duty adjustable bracket that provides solid support even up to 3-1/2 in. away from steel studs.

Cat. No.	Volume (Cu. in.)	Features Clamps	Knockouts 1/2 in. ends	1/2 in. bottom	3/4 in. ends	Pryouts ends
Device boxes – 2 1/2 in. deep – gangable – 3 in. x 2 in.						
CI3104-KSSX	16.0	–	2	2	2	–
CI3104-KSSX-5/8	16.0	–	2	2	2	–
CI3104-KSSX-NG*	16.0	–	2	2	2	–
BC3104-KSS1X-1	16.0	–	2	2	2	–
BC3104-LSSAX	16.0	BX/Loomex	–	–	–	4
BC3104-LSSAX-NG*	16.0	BX/Loomex	–	–	–	4
BC3104-LSSX	16.0	Loomex/BX	–	–	–	4
CI3104-LSS1X-1	16.0	Loomex/BX	–	–	–	4
CI3104-LSSA1X-1	16.0	BX/Loomex	–	–	–	4
CI3104-SSX	16.0	Loomex/BX	2	2	–	–
Device boxes – 2 1/2 in. deep – non-gangable – 3 in. x 2 1/4 in.						
CI1504-LSSAX	15.0	Loomex/BX	–	–	–	4
Device boxes – 3 in. deep – gangable – 3 in. x 2 in.						
CI3004-LSSAX-1	18.0	BX/Loomex	–	–	–	4
CI3004-LSSX	18.0	Loomex/BX	–	–	–	4
CI3004-LSSX-1	18.0	Loomex/BX	–	–	–	4

* Heavy-duty adjustable bracket that provides solid support even up to 3 1/2 in. away from steel studs and supplied with raised ground screws.

Cat. No.	Description
Support brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel stud boxes

347 V Boxes and power communication boxes

CI1204-LSSAX-HV

CI4204-KSSX



CI4204-LSSX

BC3104-LSSAX-LV



CI4204-LSSAX



CI4304-LSSX



CI4304-LSSAX



BC3004-LSSAX-LV



CI1204-SSX-HV



CI1204-SS1X-HV-1

CISSX-6

BC3104-LSSAX-LV-1

Cat. No.	Volume (Cu. in.)	Features Clamps	Knockouts ½ in. ends	½ in. bottom	¾ in. ends	Pryouts ends
347 V boxes – 2 ½ in. deep – gangable – 3 in. x 2 ¼ in						
CI1204-SSX-HV	19.5	–	2	–	–	–
CI1204-LSSAX-HV	19.5	BX/Loomex	–	–	–	4
CI1204-SS1X-HV	16.0	–	2	–	–	–
Power / Communication boxes – 2 ½ in. deep – pre-ganged – 3 in. x 2 in. / gang						
CI4204-KSSX	12.5 / gang	–	4	4	4	–
CI4204-LSSX	12.5 / gang	Loomex/BX	2	2	2	4
CI4204-LSSAX	12.5 / gang	BX/Loomex	2	2	2	4
CI4204-LSSAX-1	12.5 / gang	BX/Loomex	2	2	2	4
CI4304-LSSX	12.5 / gang	Loomex/BX	–	–	–	4
CI4304-LSSAX	12.5 / gang	BX/Loomex	–	–	–	4
Power / Communication boxes - 2½ in. deep - gangable - 3 in. x 2 in.						
BC3104-LSSAX-LV	16.0	BX/Loomex	–	–	–	4
BC3104-LSSAX-LV-1	16.0	BX/Loomex	–	–	–	4
Power / Communication boxes - 3 in. deep - gangable - 3 in. x 2 in.						
BC3004-LSSAX-LV	18.0	BX/Loomex	–	–	–	4

Cat. No.	Description
Support brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel stud boxes

4 in. and 4-11/16 in. square boxes and 4 in. octagonal boxes

BC52151-KSSX

BC52151-KSSX-NG*

BC52171-KSSX

BC52171-KSSX-1/2

BC52171-1-SSX-1/2

CI72171-KSSX



CI54151-KSSX

BC54151-LSSAX

BC54151-LSSAX-NG*

BC1110-SSX

CI54171-KSSX

CI54171-KSSX-5/8

BC52171-KSSXHVKIT

* Heavy-duty adjustable bracket that provides solid support even up to 3-1/2 in. away from steel studs.

Cat. No.	Volume (Cu. in.)	Clamps	1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom	Knockouts 1 in. sides	Pryouts sides
4 in. square boxes – 1 1/2 in. deep								
BC52151-KSSX	21.0	–	7	4	3	2	–	–
BC52151-KSSX-NG*	21.0	–	7	4	3	2	–	–
4 in. square boxes – 2 1/8 in. deep								
BC52171-KSSX	30.0	–	7	4	3	2	–	–
BC52171-KSSX-NG*	30.0	–	7	4	3	2	–	–
BC52171-KSSX-1/2	30.0	–	7	4	3	2	–	–
BC52171-KSSX-F1	30.0	–	6	4	2	2	–	–
BC52171-1-SSX-1/2	30.0	–	–	4	–	2	2	–
4 11/16 in. square boxes – 2 1/8 in. deep								
CI72171-KSSX	42.0	–	8	4	4	2	–	–
4 in. octagonal boxes – 1 1/2 in. deep								
CI54151-KSSX	15.0	–	2	1	2	2	–	–
BC54151-LSSAX	15.0	BX/Loomex	–	1	–	–	–	4
BC54151-LSSAX-NG*	15.0	BX/Loomex	–	1	–	–	–	4
4 in. octagonal boxes – 2 1/8 in. deep								
CI54171-KSSX	21.0	–	2	4	2	2	–	–
CI54171-KSSX-5/8	21.0	–	2	4	2	2	–	–
4 in. square – 2 1/8 in. deep								
BC52171-KSSXHVKIT	33.6	–	6	–	2	–	–	–

* Heavy-duty adjustable bracket that provides solid support even up to 3 1/2 in. away from steel studs and supplied with raised ground screws.

Cat. No.	Volume (Cu. in.)	Features: Brackets	Features: Raised Ground Screw	Knockouts: 1/2 in. ends	Knockouts: 1/2 in. bottom	Knockouts: 1/2 in. sides
4 in. square boxes – 1 1/2 in. deep						
BC1110-SSX	16.5	"SSX"	yes	7	4	3