Utility boxes and covers

CI2018

CI2018-SB

BC2020

BC2020-R

BC20-C-1

BC20-C-3

BC20-C-4

BC20-C-5

Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Bracket	Raised Ground Screw	1/2 in. ends	1/2 in. bottom	1/2 in. sides
1 1/2 in. deep – 4 in. x 2 1/4 in.						
CI2018	13.0	–	no	2	2	6
CI2018-SB	13.0	"SB"	no	2	2	3
1 7/8 in. deep – 4 in. x 2 1/8 in.						
BC2020	14.0	–	yes	2	2	6
BC2020-R	14.0	–	–	2	–	6

Cat. No.	Description
Covers – 20 Series	
BC20-C-1	For duplex receptacle
BC20-C-3	For 1 13/32 in. diameter 15 A single receptacle
BC20-C-4	Blank
BC20-C-5	For toggle switch

Note: BC2020-R can be installed on CI2018 / BC2020 Series
Covers: Device mounting screws included

Utility boxes and covers

CI1141

BC1110

CI1110-SB

BC1110-LSKO

BC1110-SSX

BC1110-R

1151 (For toggle switch)

1198 (For Decora or GFCI)

1199
(For duplex receptacle)

BC11-C-1

BC11-C-2

BC11-C-3

BC11-C-4

BC11-C-5

BC11-C-10

CI11-C-10-HV

BC11-C-4-HV

BC11-C-5-HV

Cat. No.	Volume (Cu. in.)	Features: Bracket	Features: Raised Ground Screw	Knockouts: 1/2 in. ends	Knockouts: 1/2 in. bottom	Knockouts: 1/2 in. sides
1 1/2 in. deep – 4 in. x 2 1/4 in.						
CI1141	13.0	mounting ears	no	2	2	6
1 7/8 in. deep – 4 in. x 2 3/8 in.						
BC1110	16.5	–	yes	2	2	6
CI1110-SB	16.5	“SB”	yes	2	2	3
BC1110-R	16.5	–	–	2	–	6
BC1110-LSKO	16.5	–	yes	2	2	–
BC1110-SSX	16.5	“SSX”	yes	2	2	–
2 1/8 in. deep – 4 in. x 2 1/2 in.						
1151*	18.5	–	yes	2	2	–
1198*	18.5	–	yes	2	2	–
1199*	18.5	–	yes	2	2	–

* cULus listed

Cat. No.	Description	Cat. No.	Description
Covers – 11 Series			
BC11-C-1	For duplex receptacle	BC11-C-10	Decora/GFCI
BC11-C-2	For 1 19/32 in. diameter 15 A single receptacle	CI11-C-10-HV	Decora 347 V
BC11-C-3	For 1 13/32 in. diameter 15 A single receptacle	BC11-C-4-HV	Blank 347 V
BC11-C-4	Blank	BC11-C-5-HV	For toggle switch
BC11-C-5	For toggle switch		

Note: Covers: Device mounting screws included