


CO1 Series

100 A 120/240 V; combination with or without breaker

Product specifications

- Conductor range (line and load): 6–1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead installation
- For underground installation, gutter option must be ordered (G)
- With factory-installed neutral conductor
- Suitable for 120/240 V single-phase service entrance for mobile homes, trailers, temporary services, recreational parks and other commercial and residential locations
- All units shipped complete with breaker will be supplied with either Siemens type Q (QP) OR GE type THQL (THHQL)
- Bottom compartment has provision for 2 pole circuit breaker (max 100 A) 10 Ka breakers (22 kA breaker where indicated HI) Siemens (QP, QPH), Eaton (BR), GE (TQL). Only SQD (CHOM) breakers will fit units with suffix SD.
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



| | Cat. no. | Type | Description | Dimensions (in.) | | | Weight each | |
|--------------|-------------|-------------|---|------------------|----|----|-------------|-----|
| | | | | H | W | D | lb | kg |
| 4 Jaw | | | | | | | | |
| | CO1 | Overhead | Provision for 2 pole 10 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-G | Underground | Provision for 2 pole 10 kA rated circuit breaker, complete with gutter | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-5V | Overhead | Provision for 2 pole 10 kA rated circuit breaker, comes with 5th jaw | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-60 | Overhead | Comes complete with 2 pole 60 A 10 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-60HI | Overhead | Comes complete with 2 pole 60 A 22 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-70 | Overhead | Comes complete with 2 pole 70 A 10 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-100 | Overhead | Comes complete with 2 pole 100 A 10 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-100G | Underground | Comes complete with 2 pole 100 A 10 kA rated circuit breaker, complete with gutter | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-100HI | Overhead | Comes complete with 2 pole 100 A 22 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-100HI-G | Underground | Comes complete with 2 pole 100 A 22 kA rated circuit breaker, complete with gutter | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-SD | Overhead | Provision for Square D type QO 2 pole 10 kA rated circuit breaker | 23½ | 8¼ | 4¾ | 15 | 6.8 |
| | CO1-SD-G | Underground | Provision for Square D type QO 2 pole 10 kA rated circuit breaker, complete with gutter | 23½ | 8¼ | 4¾ | 15 | 6.8 |

Note: Some local utilities require a gutter option for underground services. Order with suffix -G.

Diagrams

