


## CO22 Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with or without breaker

### Product specifications

- Conductor range: line: 6 AWG–250 kcmil, load: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead and underground services
- Factory pre-bussed from main lugs to each position
- Supplied with hub opening closure plate for underground service
- Internal locking system for covers
- Supplied with screw type sealing rings
- Factory installed 2 pole up to 22Ka breakers type A2A 10 kA or A2N 22kA (HI)
- Eaton type ED breakers
- Comes with adjustable breaker plate to accept installation of Siemens type QJ,QJH,QR,QRH, Eaton type ED and SQD type QB
- Conductor kits are available to facilitate field installation of Siemens type QJ,QJH,QR,QRH, Eaton type ED and SQD type QB, refer to page D65
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



Cat. no.	Type	Description	Position	Dimensions (in.)			Weight Each	
				H	W	D	lb	kg
<b>CO22 Left-hand entry</b>								
CO22	Combination overhead/underground*	2 Gang, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	30	17½	5½	40	18.14
CO22-200	Combination overhead/underground*	2 Gang, Comes complete with ABB type A2A 2 X 2 pole 200 A 10 kA rated circuit breaker	2	30	17½	5½	40	18.14
CO22-200HI	Combination overhead/underground*	2 Gang, Comes complete with ABB type A2N 2 X 2 pole 200 A 22 kA rated circuit breaker	2	30	26¼	5½	60	27.21
CO23	Combination overhead/underground*	3 Gang, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	30	26½	5½	60	27.21
CO23-200	Combination overhead/underground*	3 Gang, Comes complete with ABB type A2A 3 X 2 pole 200 A 10 kA rated circuit breaker	3	30	26½	5½	60	27.21
CO23-200HI	Combination overhead/underground*	3 Gang, Comes complete with ABB type A2N 3 X 2 pole 200 A 22 kA rated circuit breaker	3	30	35	5½	80	36.29
CO24	Combination overhead/underground*	4 Gang, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	30	35¼	5½	80	36.28
CO24-200	Combination overhead/underground*	4 Gang, Comes complete with ABB type A2A 4 X 2 pole 200 A 10 kA rated circuit breaker	4	30	35¼	5½	80	36.28
CO24-200HI	Combination overhead/underground*	4 Gang, Comes complete with ABB type A2N 4 X 2 pole 200 A 22 kA rated circuit breaker	4	30	43¾	5½	100	45.36

Note: Ex. CO22-XXX, suffix (XXX) can be replaced by any of the following breaker amperage options: 100, 125 or 150.



## CO22 Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with or without breaker

### Diagrams

