


CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

Product specifications

- Conductor range: line: single ½ in. stud to accommodate compression lugs (supplied by utility), load: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for load sides
- For underground service only
- Factory pre-bussed from main lugs to each position
- Internal locking system for covers
- Supplied with screw type sealing rings
- Factory installed 2 pole up to 22kA breakers type A2A 10 kA or A2N 22kA (HI)
- Comes complete with blank compartment
- Comes with adjustable breaker plate to accept installation of Siemens type QJ,QJH.QR.QRH, Eaton type ED and SQD type QB
- Conductor kits are available to facilitate field installation of Siemens type QJ,QJH.QR.QRH, Eaton type ED and SQD type QB, refer to page D65
- CO3009A-KIT (ABB), CO3009-KIT (Siemens), CO3009SD-KIT (Square D) and CO3409FB-KIT (Eaton) conductor kits available (breakers not included) see page D64
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



Cat. no.	Type	Description	Position	Dimensions (in.)			Weight each	
				H	W	D	lb	kg
CO22-U								
Left-hand entry								
CO22-U	Underground only	2 Gang with blank compartment, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	30	26¼	5½	60	27.21
CO22-200-U	Underground only	2 Gang with blank compartment, Comes complete with ABB type A2A 2 X 2 pole 200 A 10 kA rated circuit breaker	2	30	26¼	5½	60	27.21
CO22-200HI-U	Underground only	2 Gang with blank compartment, Comes complete with ABB type A2N 2 X 2 pole 200 A 22 kA rated circuit breaker	2	30	26¼	5½	60	27.21
CO23-U	Underground only	3 Gang with blank compartment, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	30	35	5½	80	36.29
CO23-200-U	Underground only	3 Gang with blank compartment, Comes complete with ABB type A2A 3 X 2 pole 200 A 10 kA rated circuit breaker	3	30	35	5½	80	36.29
CO23-200HI-U	Underground only	3 Gang with blank compartment, Comes complete with ABB type A2N 3 X 2 pole 200 A 22 kA rated circuit breaker	3	30	35	5½	80	36.29
CO24-U	Underground only	4 Gang with blank compartment, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	30	43¾	5½	100	45.36
CO24-200-U	Underground only	4 Gang with blank compartment, Comes complete with ABB type A2A 4 X 2 pole 200 A 10 kA rated circuit breaker	4	30	43¾	5½	100	45.36
CO24-200HI-U	Underground only	4 Gang with blank compartment, Comes complete with ABB type A2N 4 X 2 pole 200 A 22 kA rated circuit breaker	4	30	43¾	5½	100	45.36

Note: Ex. CO22-XXX, suffix (XXX) can be replaced by any of the following breaker amperage options: 100, 125 or 150.



CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

Diagrams

