


FA4B-6T

400 A 600 V; “all in one” transformer rated

Product specifications

- Max. single conductor 600 kcmil Cu or dual parallel conductors 250 kcmil Cu/Al
- Load and line side termination at discretion of utility
- For underground service only
- Meter socket configuration for 6 jaws
- Complete with 6 pole test switch
- Complete with 2 fuseholders and 3 A 32 V fuses
- Installation of current transformer at discretion of utility
- Two 1 in., 1¼ in., 1½ in., 2 in., 2½ and 3 in. bottom KOs
- Permanent red nameplate affixed to front cover warns that removal of meter does not isolate the load terminals; also warning to short circuit current transformer (secondary) before removal of meter
- Weatherproof Type 3R enclosure
- Primarily used in: Alberta

Note: Photo is of an installed meter socket; current transformers are not included.



FA4B-6T

Cat. no.	Description	Dimensions (in.)		Weight each	
		H	D	lb	kg
FA4B-6T	Underground, comes with 6 pole test switch	13 ³ / ₁₆	8 ⁷ / ₁₆	50	22.67

Diagrams

