




Service entrance cable fittings

Connectors and entrance heads



| | Cat. no. | Trade size (in.) | Clamping range (in.) | | Throat (in.) |
|---|----------|------------------|----------------------|------|--------------|
| | | | Min. | Max. | |
| Two-screw fittings (zinc alloy) | | | | | |
|  | CI804 | 3/8 | 0.18 | 0.64 | 0.64 |
|  | CI806 | 3/4 | 0.41 | 0.82 | 0.83 |
|  | CI808 | 1 | 0.50 | 1.04 | 1.05 |
| | CI810 | 1 1/4 | 0.56 | 1.06 | 1.37 |
| | CI812 | 1 1/2 | 0.63 | 1.60 | 1.81 |
| | CI816 | 2 | 0.86 | 2.06 | 2.05 |



CI808 / CI816
Zinc die cast locknut

CI806
Zinc die cast locknut

CI804

NOTE: 3/8 in. trade size connectors require a 1/2 in. knockout.








| | Cat. no. | Trade size (in.) |
|---|--------------|------------------|
| Service entrance heads (cast aluminum) rigid conduit | | |
|  | CIEFA-1/2 | 1/2 |
| | CIEFA-3/4 | 3/4 |
| | CIEFA-1 | 1 |
| | CIEFA-1-1/4 | 1 1/4 |
| | CIEFA-1-1/2 | 1 1/2 |
| | CIEFA-2 | 2 |
| | CIEFA-2-1/2 | 2 1/2 |
| | CIEFA-3 | 3 |
| | CIEFA-3-1/2 | 3 1/2 |
| | CIEFA-4 | 4 |
| Service entrance heads (cast aluminum) EMT | | |
|  | CIEFSA-1/2 | 1/2 |
| | CIEFSA-3/4 | 3/4 |
| | CIEFSA-1 | 1 |
| | CIEFSA-1-1/4 | 1 1/4 |
| | CIEFSA-1-1/2 | 1 1/2 |
| | CIEFSA-2 | 2 |
| | CIEFSA-2-1/2 | 2 1/2 |
| | CIEFSA-3 | 3 |
| | CIEFSA-3-1/2 | 3 1/2 |
| | CIEFSA-4 | 4 |

CIEFA-1/2 / CIEFA-4

CIEFSA-1/2 / CIEFSA-4

Service entrance head KO configuration

| Diagrams | Trade size (in.) | KO dimensions (in.) | | |
|---|------------------|---------------------|-------|--------|
| | | Small | Large | Center |
|  | 1/2 | 0.312 | - | - |
|  | 3/4 | 0.375 | 0.400 | - |
|  | 1 | 0.438 | 0.500 | - |
|  | 1 1/4 | 0.438 | 0.625 | - |
|  | 1 1/2 | 0.610 | 0.750 | 0.400 |
| | 2 | 0.750 | 1.000 | 0.525 |
| | 2 1/2 | 0.875 | 1.300 | 1.000 |
| | 3 | 1.125 | 1.750 | 1.125 |
| | 3 1/2 | 1.125 | 1.750 | 1.125 |
| | 4 | 1.125 | 1.750 | 1.125 |

1/2 in.

3/4 in.-1 1/4 in.

1 1/2 in., 2 in.

2 1/2 in., 4 in.