Roughing-in

Accessories



	_		Working load
	Cat. no.	Trade size	lb (kg.)
	"Lion" chair	ı (zinc-plated stee	1)
J-0-0*0R-R-P-P	CI8903	#2	115 (52)
CI8903 / CI8904 /	CI8904	#3	90 (40)
	"Jack" chai	n (zinc-plated stee	1)
0000000	CI8910	#10-T	43 (19)
CI8910 / CI8912	CI8912	#12	29 (13)
	"S" hooks (zinc-plated steel)	
	CI8905	#105	73 (34)



CI8905

"Screw" hooks (zinc-plated steel)		
CI8920	#M-10	90 (40)
CI8922	#M-12	115 (52)

CI8920 (2-1/2 po) / CI8922 (3 po)

	Fixture hooks -	Fixture hooks – 90° (zinc-plated steel)	
C18930	CI8930	-	115 (52)
CSA not applicable			



Fixture hooks – looped (zinc-plated steel) CI8932

Tie wire (steel – gauge no. 16)		
CI8960 (300 ft. Coil)	0.06	125 (56)





	Cat. no.	Trade size
	Duct seal compound (asbestos free)	
	CIDUCT-1	1 lb
occupa line	CIDUCT-5	5 lb

CIDUCT-1 / CIDUCT-5

Seals irregular opening from air, dust or water. Non-hardening sealant that adheres to metal, masonry, wood or plastic. Meets requirement of clause 12.018 CDN electrical code part 1. Safe and easy to use. - Non-corrosive - non-toxic - no asbestos - no unpleasant odor - will not stain or harm hands. Temperature continuous operating range: -34 °C to 88° C (-30 °F to 190° F). Minimum temperature for installation: -12 °C (10° F)