

10464 Series watertight fittings for ACWU cable



Cat. no.	Hub size (in.)	Cable jacket O.D. (in.)		Throat dia. (in.)
		Min.	Max.	
10462*	½	0.562	0.625	0.615
10464	½	0.625	0.760	0.615
10465-TB	½	0.750	0.885	0.615
10466	½	0.875	0.985	0.615
10467	¾	0.880	1.065	0.780
10468	¾	1.055	1.205	0.780
10469	1	1.187	1.375	1.000
10470	1¼	1.375	1.625	1.187
10550	1¼	1.375	1.625	1.400
10471	1¼	1.625	1.875	1.400
10472	1½	1.750	1.965	1.563
10473	1½	1.937	2.187	1.621
10551	2	2.000	2.187	2.000
10474	2	2.156	2.360	2.000
10475	2	2.350	2.565	2.000
10552	2	2.350	2.565	2.092
10476	2	2.535	2.750	2.092
10553	2½	2.535	2.750	2.437
10477	2½	2.735	2.985	2.437
10478	2½	2.970	3.220	2.437
10554	3	2.975	3.125	3.050
10555	3	3.080	3.250	3.050
10479	3	3.210	3.380	3.050
10480	3	3.310	3.480	3.050
10481	3½	3.430	3.620	3.310
10482	3½	3.560	3.750	3.310
10483	3½	3.710	3.870	3.310
10484	4	3.810	4.000	3.560
10485	4	3.930	4.120	3.670
10486	4	4.060	4.250	3.800

Note - When using fittings on single-conductor cable, aluminum fittings and aluminum locknuts must be used.

*Cat. no. 10462 not UL Listed

Materials

- Malleable iron: The above listed catalogue numbers relate to malleable iron fittings with a protective grounding sleeve for jacketed metal-clad cable.
- Aluminum: Available up to 2½ inches. To order add suffix "AL" to the catalogue number (example 10478AL).
- PVC-coated aluminum and steel: Contact your regional sales office for availability and ordering information.

Certifications

- Type HLA. CSA certified Classes I, II and III. These fittings are suitable for Class I hazardous locations when used in combination with a certified Class I hazardous location sealing fitting.
- Type OLA. UL listed. These fittings are suitable for use interlocked jacketed cable, aluminum or steel armour.

