

DuraGard waterproof connections

50 A standard service and 50 A reverse service



Device ratings and polarizations

Pole	Wire	Safety polarization (receptacle)	Voltage	Cat. no. ▼ <input type="checkbox"/>	Cat. no. ▼ <input type="checkbox"/>
Product type				Male plug	Female connector
2	3		125 V AC	9P53U1	9C53U1
2	3		250 V AC	9P53U2	9C53U2
2	3		277 V AC	9P53U3	9C53U3
2	3		480 V AC	9P53U4	9C53U4
2	3		600 V AC	9P53U5	9C53U5
2	3		through 600 V AC/250 V DC	9P53U0	9C53U0
3	4		125/250 V AC	9P54U1	9C54U1
3	4		3Ø 250 V AC	9P54U2	9C54U2
3	4		3Ø 480 V AC	9P54U4	9C54U4
3	4		3Ø 600 V AC	9P54U5	9C54U5
3	4		through 600 V AC/250 V DC	9P54U0	9C54U0

Maximum 600 V AC/250 V DC

Add suffix - / xxxx for bushing I.D. (page 64) or conduit adapter assembled.

♦ "W" suffix is watertight; "F" suffix for splash-proof spring flap cover.