

## DuraGard waterproof connections

### Safety interlocks



The only non-metallic, 22 kAIC, 30 A and 50 A series circuit breaker interlocked receptacle available today!

#### Circuit breaker interlocked outlet:

- 30 A and 50 A ranges and polarizations to 480 V AC
- 22 kA interrupt capacity breaker
- Easy handle reset after trip
- Auxiliary switch or other options

#### User friendly – Flexible mounting:

- Variable footprint mounting tabs
- Compact size fits 8" standard I-beam webs
- Conduit entry from top, bottom or side ( $\frac{3}{4}$ ", 1" or 1 $\frac{1}{4}$ " NPT)
- Large red handle with lockout access

#### Flame rated and DuraV tough housing:

- UL 94-V0 housing and interior with stainless steel components
- High-impact thermoplastic housing
- NEMA 4X construction

### Safety interlocks

Amps	Poles/wires	Voltage	Safety interlock with circuit breaker <sup>†</sup>	Circuit breaker trip rating (A)	Mating plug	Rotary controller	Replacement interior	Cat. no.
30	3P4W	125/250 V AC	9MT34U1W30B	30	9P34U1	9MI34U1WNAB	9XL34U1	
30	3P4W	3Ø 250 V AC	9MT34U2W30B	30	9P34U2	9MI34U2WNAB	9XL34U2	
30	3P4W	3Ø 480 V AC	9MT34U4W30B	30	9P34U4	9MI34U4WNAB	9XL34U4	
30	3P4W	3Ø 600 V AC	9MT34U5W30B	30	9P34U5	9MI34U5WNAB	9XL34U5	
30	3P4W	through 600 V AC/3P4W	9MT34U0W30B	30	9P34U0	9MI34U0WNAB	9XL34U0	
50	3P4W	125/250 V AC	9MT54U1W50B	50	9P54U1	9MI54U1WNAB	9XL54U1	
50	3P4W	3Ø 250 V AC	9MT54U2W50B	50	9P54U2	9MI54U2WNAB	9XL54U2	
50	3P4W	3Ø 480 V AC	9MT54U4W50B	50	9P54U4	9MI54U4WNAB	9XL54U4	
50	3P4W	3Ø 600 V AC	9MT54U5W50B	50	9P54U5	9MI54U5WNAB	9XL54U5	
50	3P4W	through 600 V AC/3P4W	9MT54U0W50B	50	9P54U0	9MI54U0WNAB	9XL54U0	

Note: 1. Change suffix for alternate trip ratings. Example: 9MT54U2W30B – 50 A, 3P4W, safety interlock with 30 A circuit breaker, conduit top entry.

♦ Change "W" to "F" for flap cap access. Example: 9MI34U2F30B – 30 A, 3P4W, safety interlock with rotary controller and flap cap.

(Minimum limit 85% of O.D. size for sealing.)

Foot and hardware replacement Kit: Cat. no. 9XLMF (non-metallic) and Cat. no. 9XLMF-SS (stainless steel).

### Diagrams

