

## Conduit hubs



### Conduit hubs

Cat. no.	Ground wire size (AWG)	Conduit/wire size
3930	#8 to #2	½ in. Conduit
3940	#8 to #2	¾ in. Conduit
3950	#8 to 3/0	1 in. Conduit
3951	#8 to 4/0	1¼ in. Conduit
3960	#8 to #4	Armored wire

Material: Malleable iron.



### Type CH – Bronze conduit hubs

- Rugged cast bronze threaded hub
- Provide positive connection between rigid conduit and water system in conjunction with “J” clamp

Cat. no.	Conduit size (in.)	Conductor range (AWG)	
		Max.	Min.
CH12	½	#6 sol.	#10 sol.
CH34	¾	2/0 str.	#10 sol.
CH1BB	1	3/0 str.	#10 sol.