

Signal reference grid connectors



Compress #8 AWG through 4/0 AWG cable

- Clamp onto pedestal posts up to 1 in. diameter square and 1¼ in. round
- Can be used as “X” or “T” configuration cable to post
- High-conductivity wrought-copper construction



Cat. no.	Conductor range (AWG)	Installing tools and die codes TBM14M and TBM15I			Colour code
		Die cat no.	Die code		
SRG8-4	#8	15527SS	29	Grey	
	#6 to #4	15528SS	33	Brown	
SRG2-1	#2 and #1	15508SS	42	Pink	
SRG10-20	1/0 and 2/0	15530SS	50	Orange	
SRG30-40	3/0 and 4/0	15511SS	54	Purple	



Secure signal reference grid wires to raised-floor support posts

- Range-taking design accepts #4 to #8 AWG grid wire and fits ¾ in. square to 1 in. round
- Lay-in feature means no kinks or bends
- Quick, easy installation
- Only one screw to tighten
- Enable grid wire to make direct, low-resistance contact with support posts
- Stamped-steel construction, zinc plated



Cat. no.	Description	Wire range (AWG)
3900 (Unit)	¾ in. square to 1 in. round	#8-#4
3900BP (Bulk pack)	¾ in. square to 1 in. round	#8-#4

