
CO22 Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with or without breaker

Product specifications

- Conductor range: line: 6 AWG-250 kcmil, load side Conductor range: for ABB SACE A1A/A1N:4-1AWG or ABB SACE A2A/A2N:1 AWG-250 kcmil. For other approved circuit breakers, see manufacturer specifications. For load side,neutral side, conductor range: 6AWG-250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead and underground services
- Factory pre-bussed from main lugs to each position
- Supplied with hub opening closure plate for underground service

- · Internal locking system for covers
- · Supplied with screw type sealing rings
- Factory installed 2 pole 10KA OR 22 KA (HI) breakers either an ABB or Siemens
- · Eaton type ED breakers
- Factory installed adjustable bracket for field installation of Siemens type QJ(L), QJH(L), QR(L) and QRH(L), SQD type QBL, Eaton type ED
- Conductor kits are available to facilitate field installation of Siemens type QJ(L), QJH(L), QR(L) and QRH(L), SQD type QBL, Eaton type ED(L), refer to page D61
- · Weatherproof Type 3R enclosure



						Dimensions (in.)			Weight Eac	
	Cat. no.	Type	Description Position		н	W	D	lb	k	
CO22	Left-hand en	ry								
	CO22	Combination overhead/ underground*	2 Gang, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	30	171/2	51/2	40	18.1	
	CO22-200	Combination overhead/ underground*	2 Gang, Comes complete with 2 X 2 pole 200 A 10 kA rated circuit breaker	2	30	171/2	5½	40	18.1	
	CO22-200HI	Combination overhead/ underground*	2 Gang, Comes complete with 2 X 2 pole 200 A 22 kA rated circuit breaker	2	30	17½	5½	60	27.2	
0 0	CO23	Combination overhead/ underground*	3 Gang, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	30	261/4	5 ½	60	27.2	
	CO23-200	Combination overhead/ underground*	3 Gang, Comes complete with 3 X 2 pole 200 A 10 kA rated circuit breaker	3	30	261/4	5 ½	60	27.2	
	СО23-200НІ	Combination overhead/ underground*	3 Gang, Comes complete with 3 X 2 pole 200 A 22 kA rated circuit breaker	3	30	261/4	5½	80	36.2	
	CO24	Combination overhead/ underground*	4 Gang, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	30	35	5½	80	36.2	
	CO24-200	Combination overhead/ underground*	4 Gang, Comes complete with 4 X 2 pole 200 A 10 kA rated circuit breaker	4	30	35	5½	80	36.2	
	CO24-200HI	Combination overhead/ underground*	4 Gang, Comes complete with 4 X 2 pole 200 A 22 kA rated circuit breaker	4	30	35	5½	100	45.3	

 $Note: Ex.\ CO22-XXX, suffix\ (XXX)\ can\ be\ replaced\ by\ any\ of\ the\ following\ breaker\ amperage\ options: 100, 125\ or\ 150.$

CO22 Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with or without breaker

Diagrams 5**½** in. Trade size - 1**½** in. Trade size 1**%** in. knockout Trade size knockout 1½, 2, 2½ and 3 in. knockout 11/4, 11/2, 1% in. **½** in. 2 and 2½ in. 1 place 2 places 4 places 71/s in. 2¼ in. 2**%** in. 13/16 in. 4% in. 1% in. 26**15/16** in. 30 in.