


## CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

### Product specifications

- Conductor range: line: single 1/2 in. stud to accommodate compression lugs, load side conductor range: for ABB SACE A1A/A1N:4-1AWG or ABB SACE A2A/A2N:1 AWG-250 kcmil. For other approved circuit breakers, see manufacturer specifications. For load side, neutral conductor range: 6AWG - 250 kcmil
- Aluminum tunnel type connectors for load sides
- For underground service only
- Factory pre-bussed from main lugs to each position
- Internal locking system for covers
- Supplied with screw type sealing rings
- Factory installed 2 pole 10KA OR 22 KA (HI) breakers either an ABB or Siemens
- Comes complete with blank compartment
- Factory installed adjustable bracket for field installation of Siemens type QJ(L), QJH(L), QR(L) and QRH(L), SQD type QBL, Eaton type ED
- Conductor kits are available to facilitate field installation of Siemens type QJ(L), QJH(L), QR(L) and QRH(L), SQD type QBL, Eaton type ED(L), refer to page D61
- CO3009A-KIT (ABB), CO3009-KIT (Siemens), CO3009SD-KIT (Square D) and CO3409FB-KIT (Eaton) conductor kits available (breakers not included) see page D61
- Weatherproof Type 3R enclosure



Cat. no.	Type	Description	Position	Dimensions (in.)			Weight each	
				H	W	D	lb	kg
<b>Left-hand entry</b>								
CO22-U	Underground only	2 Gang with blank compartment, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	30	26¾	5½	60	27.21
CO22-200-U	Underground only	2 Gang with blank compartment, Comes complete with 2 X 2 pole 200 A 10 kA rated circuit breaker	2	30	26¾	5½	60	27.21
CO22-200HI-U	Underground only	2 Gang with blank compartment, Comes complete with 2 X 2 pole 200 A 22 kA rated circuit breaker	2	30	26¾	5½	60	27.21
CO23-U	Underground only	3 Gang with blank compartment, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	30	35	5½	80	36.29
CO23-200-U	Underground only	3 Gang with blank compartment, Comes complete with ABB type A2A 3 X 2 pole 200 A 10 kA rated circuit breaker	3	30	35	5½	80	36.29
CO23-200HI-U	Underground only	3 Gang with blank compartment, Comes complete with ABB type A2N 3 X 2 pole 200 A 22 kA rated circuit breaker	3	30	35	5½	80	36.29
CO24-U	Underground only	4 Gang with blank compartment, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	30	43¾	5½	100	45.36
CO24-200-U	Underground only	4 Gang with blank compartment, Comes complete with 4 X 2 pole 200 A 10 kA rated circuit breaker	4	30	43¾	5½	100	45.36
CO24-200HI-U	Underground only	4 Gang with blank compartment, Comes complete with 4 X 2 pole 200 A 22 kA rated circuit breaker	4	30	43¾	5½	100	45.36

CO22-U



Note: Ex. CO22-XXX, suffix (XXX) can be replaced by any of the following breaker amperage options: 100, 125 or 150.

## CO22-U Series

200 A (main lugs), 200 A per position, single-phase 120/240 V; multiple position combination with compartment with or without breaker

### Diagrams

