

## Installation tools



### Portable heat shrink torch

Separate fuel- and air-flow controls enable precise adjustment of flame and temperature to 1,371 °C (2,500 °F).

- 1,371 °C (2,500 °F) output capacity satisfies virtually any heat-shrink, brazing or soldering requirement
- Dual fuel- and air-flow controls enable separate adjustment of temperature and flame precision
- Brass and steel construction provides durability

### Specifications

- Dimensions (without base): 3.9 in. L x 1.4 in. W x 5.4 in. H
- Weight (when filled): 9.88 oz.
- Fuel tank capacity: 2.03 fl. oz.
- Operating time (per full fuel tank): Up to 220 minutes

### Portable heat shrink torch

Cat. no.	Description	Std. pkg. qty.
WT-PTORCH	Shrink-Kon portable heat-shrink torch	1

Order multiple is std. pkg.



### Electric heat gun

- UL Listed and CSA certified
- 232 °C to 649 °C heat range (450 °F to 1,200 °F)
- 120 VAC 60 Hz

### Electric heat gun



Cat. no.	Description	Std. pkg. qty.
WT1400	Dual temp. heat gun. 600 °F / 900 °F, 1,300 W, 120 VAC 60 Hz	1

Order multiple is std. pkg.