


## 833

The Marrette 833 is an outstanding wire connector with an ergonomic wing design that can take a wide range of wire combinations from #22 to #8 AWG.



Can also be used with  
1/2 in. or 13 mm nut driver.

#### External cap

- Ergonomic wing design gives you a comfortable grip and more torque than the competition.
- The ergonomic shape reduces finger fatigue from repetitive installations.
- The ergonomic wing shape allows excellent torque grip for your fingers as well as the option to use a standard 1/2 in. or 13 mm hex driver to help twist the wire connector.
- Made of tough durable polypropylene and 105 °C (221 °F) rated to withstand high installation pressures.
- Deep, wide throat ensures full insulation coverage.

Exclusive Live Action variable volume spring expands to accommodate even more wires with less twisting effort compared to other wide range wire connectors.

#### Inner spring

- Range: #22 to #8 AWG with no pre-twisting.
- The square wire spring construction and funnel design give a positive pressure conductor grip for solid or stranded wires.
- Approved for circuits up to 600 V and lighting fixtures and signs up to 1,000 V.
- For copper conductor only.
- Convenient packaging – sized right and job-site ready.

## 833

### Ordering information

Model	Colour	AWG wire range							
		22	20	18	16	14	12	10	8
833	Yellow								Min. 2 #22 + 1 #20, Max. 3 #10

#### Drivers

TOOL-WING

Driver for winged Marrette connectors

Note: Refer to pages A38-A40 for related wire combination reference guide.

#### Packaging options



Cat. no.	Packaging format	Quantity per package	Std. pkg. (min./mult.)
<b>833</b>			
833P	Propak	100	1,000 units
833KP	Resealable bag	500	5,000 units
833D	Flip-pak	500	500 units
833M	Flip-pak	1,000	1,000 units
833BK	Flip-pak	10,000	10,000 units
833BAR	Barrel	25,000	25,000 units



#### Packaging options

Cat. no.	Packaging format	Quantity per package	Std. pkg. (min./mult.)
<b>833</b>			
833-JAR200	Plastic jar	200	200 units
833-JAR400	Plastic jar	400	400 units
833-JAR1000	Plastic jar	1,000	1,000 units