
XTP

The Marrette XTP is a high quality, twist-on wire connector with a unique spring and cap grip design that sets it apart from the competition.





External cap

- Made of tough, durable polypropylene and 105 °C (221 °F) rated to withstand high installation pressures.
- Posi-Grip surface combines a matte finish with closely-spaced, deep grooves for superior twisting power, even when hands are greasy or damp.
- Deep, wide throat ensures full insulation coverage.
- Threaded entry helps guide large wire bundles into the spring chamber.
- · Colour-coded for quick and easy size selection.

Inner spring

- Exclusive Live Action variable volume spring expands to accommodate more wires with less twisting effort compared to other connectors with a "fixed spring" design.
- Model nos. 329 and 330 have a round spring, while 331, 333 and 335 have a square wire spring construction that gives a positive conductor bite to solid or stranded wires.
- Unique copper-coated spring helps resist corrosion.
- Model nos. 329 and 330 are approved for circuits up to 300 V only. Model nos. 331, 333, 335 and 822 are approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
- For copper conductor only.
- Convenient packaging sized right and job-site ready.

A11

XTP

Ordering information

		,		,	,		,	AWG wi	ire range
Model	Colour	22	20	18	16	14	12	10	8
329	Grey		Min.	1 #22 + 1 #20, M	ax. 2 #16				
330	Blue			Min.:	1 #22 + 1 #20, M	ax. 3 #16			
331	Orange				Min. 2 #18, M	ax. 3 #14			
333	Yellow						Min. 2 #18, M	ax. 2 #10	
335	Red						Min. 2 #14, M	ax. 3 #10	
822*	Blue						Min.	2 #22 + 1 #20, M	ax. 2 #8

Note: Refer to pages A32-A34 and A37-A38 for related wire combination reference guides. *UL not applicable.

Packaging options



Packaging options						
Cat. no.	Packaging format	Quantity per package	Std. pkg. (min./mult.)			
329		,				
329P	Propak	100	1,000 units			
329BP	Bulk box	1,000	1,000 units			
329BK	Flip-pak	10,000	10,000 units			
330		,				
330P	Propak	100	1,000 units			
330BP	Bulk box	1,000	1,000 units			
330BK	Flip-pak	10,000	10,000 units			
331						
331P	Propak	100	1,000 units			
331D	Flip-pak	500	2,000 units			
331KP*	Resealable bag	500	5,000 units			
331M*	Flip-pak	1,000	1,000 units			
331BK*	Flip-pak	10,000	10,000 units			
331BAR*	Barrel	45,000	45,000 units			
333		·				
333P	Propak	100	1,000 units			
333KP**	Resealable bag	500	5,000 units			
333D**	Flip-pak	500	500 units			
333M**	Flip-pak	1,000	1,000 units			
333BK**	Flip-pak	10,000	10,000 units			
333BAR**	Barrel	25,000	25,000 units			
335		·				
335P	Propak	100	1,000 units			
335Q [†]	Flip-pak	200	800 units			
335D†	Flip-pak	500	500 units			
335BK	Flip-pak	7,000	7,000 units			
822		,				
822Q	Flip-pak	200	800 units			
822D*	Flip-pak	500	500 units			
822BK**	Flip-pak	8,000	8,000 units			
822BAR**	Barrel	20,000	20,000 units			
Drivers						
TOOL 331	Plastic driver to install Model 331 (included in all)*					
TOOL 333	Plastic driver to install Model 333 and 822 (included in all packs)**					
TOOL 335	Plastic driver to install Model 335 (included in all packs) †					