

New product

EAEC Series

Pictogram extruded aluminum edge-lit combo




Features

- Extruded aluminum trim plate
 - Universal wall and ceiling surface or recessed mounting
 - Includes pictogram panels for single and double face applications
 - High power LED lamps
 - Lamp heads are fully adjustable
 - High temperature long life Ni-MH battery
 - 120/347VAC 60Hz
 - CSA C22.2 no.141-15 approved
 - Standard with diagnostics
 - Unit has a one-year limited warranty
- Warranty details at: www.emergi-lite.ca**

Photometric performance

Series	Spacing center-to-center (feet)	7.5' mounting height
EAEC-2H0		30'



Power consumption

Model	AC specs	DC specs
EAEC-2H0	120/347VAC, 60 Hz, 3W	Ni-MH battery Minimum 90 minutes

Ordering information

Series	Face/arrow (universal mounting)	Colour	Lamp
EAEC	Blank= universal faces	Blank= factory white	-2H0= 2 high output LED lights

Example: EAEC-2H0

Dimensions

Dimensions are approximate and subject to change.



< Pictogram LEFT from here




Pictogram STRAIGHT from here



Pictogram > RIGHT from here

Surface mount



Option 1

Option 2

Recessed mount

