

RFX LED SERIES

Hazardous Location

FEATURES

- CSA Certified for use in hazardous locations:
- Class I, Divisions 1 and 2, Groups C, D Class II, Divisions 1 and 2, Groups E, F, G
- Class III
- High efficacy LED lamps
- Die-cast aluminum body with grey epoxy powder coat finish
- Clear, impact and heat resistant prismatic glass globe
- Available in 6, 12, 24 and 120V
- Available with single-lamp or twin-lamp combination
- T6 maximum 85°C (185°F) temperature rating
- Meets or exceeds C22.2 No.137-M1981
- Meets or exceeds CSA 22.2 No.141 See warranty details at: www.tnb.ca/en/brands/ready-lite





TYPICAL SPECIFICATIONS

Supply and install the Ready-Lite® RFX LED Series of hazardous location remote heads. The head housing will
be die-cast aluminum with grey epoxy powder coat finish. The lens shall be a clear, impact and heat resistant
prismatic glass globe. The head shall be factory sealed. External seals shall not be required. The remote shall
come complete with a mounting connection and includelamp(s) rated V W. The
remote head shall be suitable for Class, Division, Group
The remote unit shall be Ready-Lite® model:

REPLACEMENT LAMPS

MODEL	TYPE	VOLT/WATT	
580.0097-RL	LED	6V-4W	
580.0122-RL		6V-5W	
580.0104-RL		12V-5W	
580.0106-RL		12V-6W	
580.0098-RL		24V-4W	
580.0095-RL		120V-4W	







CL. I, DIV. 1 & 2, GR. C, D

CL. III

CL. II, DIV. 1 & 2, GR. E, F, G



Dimensions are approximate and subject to change.





RFX LED SERIES


CEILING MOUNT


Hazardous Location














ORDERING INFORMATION

SERIES	LAMP TYPE	SEVERITY CODES	LAMP WATTAGE/TYPE	MOUNTING	
RFXQ= single remote, one lamp RFXQ-P2= double remote, one lamp each¹ RFXQ2= single remote, two lamps	Blank= MR16 LED	Blank= Cl. I, Div. 1 & 2, Gr. C, D Cl. II, Div. 1 & 2, Gr. E, F, G Cl. III S2= Cl. I, Div.1, Gr. C, D	LD1= MR16 LED, 6V-4W LD2= MR16 LED, 6V-5W LD7= MR16 LED, 12V-4W LD9= MR16 LED, 12V-5W LD10= MR16 LED, 12V-6W LD13= MR16 LED, 24V-4W LD25= GU10 LED, 120V-4W	C= ceiling mount P= pendant mount W= wall mount	
1 pendant mount only					