



SM-CX5000 SERIES

Extruded Aluminum
Combination Unit - 6/12V



TYPICAL SPECIFICATIONS

Supply and install the **Ready-Lite® SM-CX5000** LED Exit Sign and power pack combination series. The exit housing shall be constructed of rugged extruded aluminum. The faceplate shall be constructed of extruded aluminum. The Exit Sign shall have a maximum depth of 2-1/2". The faceplate(s) shall come standard with knockout chevrons. The light source shall be light emitting diodes (LED). The LED lamps shall provide illumination in normal and emergency operation and shall be mounted inside the exit housing. An LED-sensitive diffuser shall be mounted behind the legend to provide the 6" high by 3/4" stroke letters with even illumination. The power pack shall be a completely self-contained emergency unit with its own charger and rechargeable battery. The housing shall be made of steel, painted factory white. The unit shall be designed to furnish exit illumination from the normal AC source. When a power failure occurs the mounted heads along with the Exit Sign are illuminated in emergency mode for a minimum of 30 minutes. The power pack is furnished with a test switch and high charge pilot light and is available as either 18, 36 or 72W. The heads shall require no tools to adjust and aim. The heads will be constructed of a durable thermoplastic construction and use 6V, 4W LED lamps or as otherwise specified. The Exit Sign shall be CSA-C860 approved and meets CSA 22.2 No. 141.


The equipment shall be **Ready-Lite®** Model: _____ .

WIRE GUARDS

460.0081-RL	wall mount
460.0060-RL	ceiling mount

DIMENSIONS

Dimensions are approximate and subject to change.



POWER CONSUMPTION AND UNIT RATING

MODEL	AC SPECS	WATTAGE CAPACITY				
		30MIN	1H00	1H30	2H00	4H00
Exit Sign Module	less than 1.5W	-	-	-	-	-
SM18-6V	0.15/0.05 A	18	10	7	6	3
SM36-6V	0.15/0.05 A	36	21	15	12	6
SM36-12V	0.18/0.07 A	36	21	15	12	6
SM72-12V	0.15/0.05 A	72	42	30	24	12

ORDERING INFORMATION

SERIES	NUMBER OF HEADS	HEAD STYLE AND WATTAGE	FACES/MOUNTING	VOLTAGE	COLOUR	OPTIONS
SM18= 6V-18W* SM36= 6V, 12V-36W	Blank= no heads 1= one head 2= two heads	LD1= MR16 LED, 6V-4W LD2= MR16 LED, 6V-5W LD7= MR16 LED, 12V-4W LD9= MR16 LED, 12V-5W LD10= MR16 LED, 12V-6W	-CX5100= single face, universal mounting -CX5200= double face, universal mounting	Blank= 120/347VAC, 6VDC* L062= 277VAC, 6VDC* L12U= 120/347VAC, 12VDC L122= 277VAC, 12VDC	Blank= factory white BA= brushed aluminum* BK= black TA= textured aluminum* *Black heads	Blank= no options AD= auto-diagnostics* ADN= auto-diagnostics, non-audible* NEXRF= wireless NEXUS® system interface* D3= time delay (15 mins.) G= green legend *Not available for 6V-72W *Not all options available with NEXUS® System. Please consult your sales representative

*Available in 6V only

*18W and 36W only.

EXAMPLE: SM18LD1-CX5100