



## RL40M SERIES

Remote Fixture

### FEATURES

- Quality illumination requires fewer fixtures
  - Clear polycarbonate UV and impact resistant lens with optional tamper-proof screws to prevent tampering
  - Easy lamp replacement
  - CSA certified to C22.2 No.141-15
  - Modern design will blend into surroundings
  - Selection of Die-Cast or polycarbonate back plate
  - For indoor use only
- See warranty details at: [www.tnb.ca/en/brands/ready-lite](http://www.tnb.ca/en/brands/ready-lite)

### TYPICAL SPECIFICATIONS

Supply and install **Ready-Lite® RL40M Series** remote emergency lighting. These remote fixtures will consist of either single or double lamp configurations as specified and include a UV resistant fire retardant polycarbonate back plate and a clear heavy-duty UV resistant polycarbonate light cover. The remote fixture shall be certified to CSA C22.2 No.141-15. The head(s) shall be fully adjustable and be equipped with high efficiency LED lamp(s) of \_\_\_\_ V, \_\_\_\_ W.

The remote unit shall be **Ready-Lite®** model: \_\_\_\_\_.

### WIRE GUARDS

460.0029-RL	wall mount
-------------	------------


### REPLACEMENT LAMPS

MODEL	LAMP TYPE	VOLTAGE/WATTAGE
580.0097-RL	MR16, LED	6V-4W
580.0122-RL	MR16, LED	6V-5W
580.0093-RL	MR16, LED	12V-4W
580.0104-RL	MR16, LED	12V-5W
580.0106-RL	MR16, LED	12V-6W
580.0098-RL	MR16, LED	24V-4W
580.0100-RL	MR16, LED	24V-6W

See Guardian list of lamps

### DIMENSIONS

Dimensions are approximate and subject to change.



### ORDERING INFORMATION: RL40MP

SERIES	NUMBER OF LAMPS	LAMP TYPE/VOLTAGE/WATTAGE	COLOUR	OPTIONS
RL40MP= polycarbonate back plate	1= one lamp 2= two lamps	-LD1= MR16 LED, 6V-4W -LD2= MR16 LED, 6V-5W -LD7= MR16 LED, 12V-4W -LD9= MR16 LED, 12V-5W -LD10= MR16 LED, 12V-6W -LD13= MR16 LED, 24V-4W	Blank= factory white BK= black GY= grey  Other colours available.	Blank= no options T= tamper-proof screws <sup>1</sup>  <sup>1</sup> 690.0454-RL= tamper-proof bit (sold separately)

EXAMPLE: RL40MP1-LD7

### ORDERING INFORMATION: RL40M

SERIES	NUMBER OF LAMPS	LAMP TYPE/VOLTAGE/WATTAGE	COLOUR	OPTIONS
RL40M= die-cast	1= one lamp 2= two lamps	-LD1= MR16 LED, 6V-4W -LD2= MR16 LED, 6V-5W -LD7= MR16 LED, 12V-4W -LD9= MR16 LED, 12V-5W -LD10= MR16 LED, 12V-6W -LD13= MR16 LED, 24V-4W -LD14= MR16 LED, 24V-6W -LD26= MR16 LED, 120V-4W	Blank= factory white BK= black GY= grey  Other colours available.	Blank= no options T= tamper-proof screws <sup>1</sup>  <sup>1</sup> 690.0454-RL= tamper-proof bit (sold separately)

EXAMPLE: RL40M1-LD10