



LEGEND™ SERIES

Surface Designer Series



TYPICAL SPECIFICATIONS

The contractor will supply and install **Ready-Lite® Legend™ Series** remote heads. These remote heads will consist of either single, double or triple head configurations according to the design. Remote heads will be constructed of durable powder coated, Die-Cast aluminum and use LED light sources.

The remote fixtures shall be certified to CSA C22.2 No.250.

The unit shall be **Ready-Lite®** model: _____.

WIRE GUARDS

460.0029-RL	wall mount single remote
460.0032-RI	wall mount double remote
460.0078-RL	wall mount triple remote

FEATURES


- Contemporary, enduring design
 - Available in 1, 2 or 3 head configurations
 - Highly resistant powder-coated, Die-Cast aluminum construction
 - LED lamps: 4W, 5W and 6W
 - CSA certified to C22.2 No.141-15
- See warranty details at: www.tnb.ca/en/brands/ready-lite

REPLACEMENT LAMPS

MODEL	LAMP TYPE	VOLTAGE-WATTAGE
580.0097-RL	MR16, LED	6V-4W
580.0122-RL	MR16, LED	6V-5W
580.0093-RL	MR16, LED	12V-4W
580.0104-RL	MR16, LED	12V-5W
580.0106-RL	MR16, LED	12V-6W
580.0098-RL	MR16, LED	24V-4W
580.0100-RL	MR16, LED	24V-6W
580.0113-RL	MR16, LED	120V-4W
580.0125-RL	MR16, LED	120V-7W

DIMENSIONS

Dimensions are approximate and subject to change.



ORDERING INFORMATION

SERIES	# OF HEADS	COLOUR	LAMP TYPE/VOLTAGE/WATTAGE
RL150= closed	Blank= one head D= two heads T= three heads	-B= black Blank= white	-LD1= MR16 LED, 6V-4W -LD2= MR16 LED, 6V-5W -LD7= MR16 LED, 12V-4W -LD9= MR16 LED, 12V-5W -LD10= MR16 LED, 12V-6W -LD13= MR16 LED, 24V-4W -LD14= MR16 LED, 24V-6W -LD26= MR16 LED, 120V-4W -LD27= MR16 LED, 120V-7W

EXAMPLE: RL150-LD9