

## Hal-Free Riser-Gard

### Product overview



Hal-Free Riser-Gard is a halogen-free nonmetallic flexible raceway for use in riser and general purpose applications. In the event of a fire, this product will not release halogen elements into the air, which makes it ideal for applications in tunnels, laboratories and high-tech environments.

Custom lengths and split ducts are available upon request.

Hal-free Riser-Gard is available in white only.

- Storage and handling: -20 °C to 66 °C (-4 °F to 150 °F)
- No UV protection (not suitable for outdoor use)
- Do not store outside
- Free from halogen elements
- Available in sizes 1 in. through 2 in.
- Available in white only
- Sequentially marked footage

#### Applications:

Riser and general purpose

#### Technical information:

UL Standard 2024	Max. value
Maximum flame propagation	3 ft. 6 in.
Maximum air temperature	197 °C (387 °F)

#### Standard stock – Reels



Cat. no.	Size (in.)	Colour	Nom. I.D. (in.)	Nom. O.D. (in.)	Pull tape	Reel size (F x W) (in.)	Reel type	Reel length (ft.)	Reel wt. (lb)	Product wt. per 100 ft. (lb)
HF4X4C-5000	1	White	1.049	1.365	900 lb	72 x 41	Wood	5,000	310	7.5
HG4X4C-4000	1¼	White	1.250	1.550	900 lb	72 x 41	Wood	4,000	310	7.5
HH4X4C-2000	1½	White	1.500	1.850	900 lb	66 x 41	Wood	2,000	250	12
HJ4X4C-2000	2	White	2.000	2.425	900 lb	82 x 41	Wood	2,000	365	21