Multi-Gard

PVC boreable conduit







Benefits

- Withstands pulling and bending forces of directional drilling
- · Fast assembly
- Eliminates labor related to gluing and screwing joints together
- For bores up to 500 feet
- Innerducts: 3-way or 4-way
- Easy to handle 20-foot lengths
- Type: Type 40 PVC outerduct
- Size: 4 in.
- Prelubricated innerducts
- Strong water-tight joints without cement
- Fits standard Schedule 40 fittings
- Compatible with Multi-Gard Type 40 PVC products

Cat. no.	Description	Length (ft.)	O.D. (in.)	Innerduct I.D. (in.)	Pkg. qty (ft./ bundle)	Bundles per truckload	Feet per truckload	Wt. per 100 ft. (lb)	Min. bend radius (ft.)	Seal pressure rating (psi)	Max. pull rating (lb)
MFSS3B-020	3-way Boreable Multi-Gard	20	4.50	1.50	520	28	14,560	561	65	75	5,000
MFSS4B-020	4-way Boreable Multi-Gard	20	4.50	1.19	520	28	14,560	565	65	75	5,000