

Accessories

Miscellaneous components




Fig. 1

Miscellaneous hangers

- Rod hanger with or without thread impression available for ¼ in. and ⅜ in. threaded rod

Miscellaneous hangers

Cat. no.	Fig. no.	Description	Static load limit (lb)	Qty. per box
F-HB8	1	Rod & wire hanger, #8 wire	160	100
SSF-HB1/4	1	Rod & wire hanger, ¼ in. plain rod	160	100
SSF-HB3/8	1	Rod & wire hanger, ⅜ in. plain rod	160	100



Fig. 1




Fig. 3

Miscellaneous hangers

- Rod hanger available for ¼ in. and ⅜ in. threaded rod with or without thread impression
- Various steel brackets with ¼ in. holes and galvanized finish

Miscellaneous hangers



Cat. no.	Fig. no.	Description	Static load limit (lb)	Qty. per box
SSF-HOB	2	Offset bracket with ¼ in. hole	160	100
SSF-HSAB	3	Short angle bracket with ¼ in. hole	160	100
SSF-HFB*	4	Flat bracket with ¼ in. hole	160	100
SSF-TA7*	5	For T-grid, with 1 in. snap-in conduit clip	-	100



Fig. 2




Fig. 3



Fig. 4



Fig. 5

*UL not applicable

Accessories

Miscellaneous components




Fig. 1

Pipe sleeve positioner

- Provides secure positioning of pipe sleeve for concrete pouring of wall and floor forms
- Accommodates up to Schedule 80 pipe wall thicknesses
- Installs easily with a hammer

Pipe sleeve positioner

Cat. no.	Fig. no.	Sleeve dia. (in.)	Description/wall thickness	Qty. per box
SSF-MPS	1	All	Pipe sleeve positioner, $\frac{3}{16}$ in. and under	100
SSF-MPS	1	2-6	Pipe sleeve positioner, Schedule 40 Pipe	100
SSF-BF1/2	1	6	Pipe sleeve positioner, Schedule 80 Pipe	100
SSF-BF1/2	2	8-10	Pipe sleeve positioner, Schedule 40 Pipe	100
SSF-BF3/4	2	9-14	Pipe sleeve positioner, Schedule 80 Pipe	100




Fig. 1

Fig. 2

Accessories

Miscellaneous components




Fig. 1 and 2

S-hook and jack chain

- Order S-hook and jack chain with your Steel City spring steel fasteners to save on freight, energy and purchase orders

S-hook and jack chain

Cat. no.	Fig. no.	Trade size	Description	Static load limit (lb)	Qty. per box/per foot
CI-8905	1	–	S-hook	90	100
CI-8903	2	#2	Jack chain	115	100
8903SP2	2	#2	Jack chain	115	200
8903SP5	2	#2	Jack chain	115	500
CI-8904	2	#3	Jack chain	90	100
8904SP2	2	#3	Jack chain	90	200
8904SP5	2	#3	Jack chain	90	500
CI-8910	2	#10-T	Jack chain	43	50
8910SP2	2	#10-T	Jack chain	43	200
8910SP5	2	#10-T	Jack chain	43	500
CI-8912	2	#12	Jack chain	29	50



Fig. 1

Fig. 2

Accessories

Miscellaneous components




Fig. 1

Signal reference grid wire clamp

- Supports signal reference grid wires below computer room floors
- One fastener supports wire sizes #8 stranded (0.146 in.) to #4 stranded (0.232 in.)
- Fits post sizes 3/4 in. to 1 in. round or square

- Slots in fastener grip wire provide positive contact with post
- Clamps grid wire directly to post, allowing a low resistance connection across bare metal contacts
- Installs easily with a screw driver or nut driver

Signal reference grid wire clamp



Cat. no.	Fig. no.	Description	Qty. per box
3900	1	Signal reference grid wire clamp	100




Fig. 1




Fig. 2

Deck hanger

- Easy method to hang items below decking
- Requires pre-drilled hole 1/4 in. diameter
- Works for material thicknesses up to 1/8 in.

Deck hanger

Cat. no.	Fig. no.	Description	Qty. per box
SSF-MNH	2	Deck hanger clip	100




Fig. 2