



EF40 & EF40P Series

Remote Fixture


FEATURES

- Quality illumination requires fewer fixtures
 - Clear polycarbonate UV and impact resistant lens with optional tamper-proof screws to prevent tampering.
 - Easy lamp replacement
 - Modern design will blend into surroundings
 - Selection of Die-Cast or polycarbonate back plate
 - For indoor use only
 - CSA certified to C22.2 No. 141-15
- See warranty details at: www.tnb.ca/en/brands/emergi-lite



DIMENSIONS

Dimensions are approximate and subject to change.



TYPICAL SPECIFICATIONS

Supply and install **Emergi-Lite® EF40P Series** remote emergency lighting. These remote fixtures will consist of either single or double lamp configurations as specified and include a UV resistant fire retardant polycarbonate back plate and a clear heavy-duty UV resistant polycarbonate light cover.

The remote fixture shall be certified to CSA C22.2 No. 141.

The head(s) shall be fully adjustable and be equipped with high efficiency LED lamp(s) of ____ V, ____ W.

The remote unit shall be **Emergi-Lite®** model: _____.

WIRE GUARDS

460.0029-E	Wall Mount
------------	------------

REPLACEMENT LAMPS

MODEL	LAMP TYPE	VOLTAGE/WATTAGE
580.0097-E	MR16 LED	6V-4W
580.0122-E	MR16 LED	6V-5W
580.0093-E	MR16 LED	12V-4W
580.0098-E	MR16 LED	24V-4W
580.0100-E	MR16 LED	24V-6W
580.0104-E	MR16 LED	12V-5W
580.0106-E	MR16 LED	12V-6W

ORDERING INFORMATION: EF40P

SERIES	NUMBER OF LAMPS	LAMP TYPE	COLOUR	LAMP TYPE/VOLTAGE/WATTAGE	OPTIONS
EF40P= polycarbonate	Blank= one lamp D= two lamps	M= MR16	Blank= factory white B= black G= grey Other colours available.	LA= MR16 LED, 6V-4W LB= MR16 LED, 6V-5W LG= MR16 LED, 12V-4W LI= MR16 LED, 12V-5W LJ= MR16 LED, 12V-6W LL= MR16 LED, 24V-4W	Blank= no option T= tamper-proof screws ¹ ¹ 690.0454-E= tamper-proof bit (sold separately)

EXAMPLE: EF40PDMBLI

ORDERING INFORMATION: EF40

SERIES	NUMBER OF LAMPS	LAMP TYPE	COLOUR	LAMP TYPE/VOLTAGE/WATTAGE	OPTIONS
EF40 = die-cast	Blank= one lamp D= two lamps	M= MR16	Blank= factory white B= black G= grey Other colours available.	LA= MR16 LED, 6V-4W LB= MR16 LED, 6V-5W LG= MR16 LED, 12V-4W LI= MR16 LED, 12V-5W LJ= MR16 LED, 12V-6W LL= MR16 LED, 24V-4W LM= MR16 LED, 24V-6W LW= MR16 LED, 120V-4W	Blank= no option T= tamper-proof screws ¹ ¹ 690.0454-E= tamper-proof bit (sold separately)

EXAMPLE: EF40DMLI