

NuTek Nonmetallic boxes



WSW



WSW-BX



WSW-N



2-WSW



3-WSW



4-WSW



WSW-FC



WOCT



WOCT-FC



WRD



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2³/₄ in. deep - 3³/₄ in. high – device boxes						
WSW	18.0	2 ¹ / ₄	–	–	4	Nonmetallic sheathed cable
WSW-BX	18.0	2 ¹ / ₄	5	4 ¹ / ₄	4	AC90-Armoured cable
WSW-N	18.0	2 ¹ / ₄	–	–	4	Nonmetallic sheathed cable
2-WSW	33.0	4	5	5 ¹ / ₂	8	Nonmetallic sheathed cable
3-WSW	48.0	5 ³ / ₄	5	7 ¹ / ₂	12	Nonmetallic sheathed cable
4-WSW	67.0	7 ⁵ / ₈	5	8 ³ / ₄	16	Nonmetallic sheathed cable
WSW-FC	18.0	2 ¹ / ₄	–	–	4	Nonmetallic sheathed cable
2³/₄ in. deep - 3³/₄ in. high – 4 in. wide – ceiling boxes						
WOCT	26.0	–	–	–	4	Nonmetallic sheathed cable
WOCT-FC	26.0	–	5 ¹ / ₄	–	4	Nonmetallic sheathed cable
3 in. deep - 4⁷/₈ in. high – 4⁷/₈ in. wide – oven and dryer						
WRD	61.0	–	6 ⁷ / ₈	6 ⁷ / ₈	4	Nonmetallic sheathed cable

NuTek Nonmetallic boxes

Airtight model



F-WSW



FWSWBX



2-FWSW



3-FWSW



4-FWSW



FWOCT



FWRD



WSW-P



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2 3/4 in. deep - non-gangable - 3 3/4 in. high – device boxes						
F-WSW	18.0	2 1/4	–	–	4	Nonmetallic sheathed cable
FWSWBX	18.0	2 1/4	5	4 1/4	4	AC90-Armoured cable
2-FWSW	33.0	4	5	5 1/2	8	Nonmetallic sheathed cable
3-FWSW	48.0	5 3/4	5	7 1/2	12	Nonmetallic sheathed cable
4-FWSW	67.0	7 5/8	5	8 3/4	16	Nonmetallic sheathed cable
2 3/4 in. deep - 3 3/4 in. high – 4 in. wide – ceiling box						
FWOCT	26.0	–	5 1/4	–	4	Nonmetallic sheathed cable
3 in. deep - 4 7/8 in. high – 4-7/8 in. wide – oven and dryer						
FWRD	61.0	–	6 7/8	6 7/8	4	Nonmetallic sheathed cable

Cat. No.	Description
Partition	
WSW-P	Voltage partition – for 2-FWSW, 2-FWSW, 4-FWSW and 4-FWSW only

Note: CEC 2012 rule 30-302: 4) Where the weight of a luminaire does not exceed 23 kg (50 lb), the luminaire shall be permitted to be supported by a ceiling outlet box attached directly to the building structure or by a ceiling outlet box attached to a bar hanger. Requires that a ceiling-mounted luminaire weighing 23 kg or less be supported on a ceiling outlet box attached directly to the building structure.

A bar hanger may also be used to attach a ceiling box to the building structure when the luminaire weighs 23 kg or less.

NuTek Nonmetallic boxes

Fire resistance rating: 2 hours



WSW-US



F-WSW-US



2WSW-US



2-FWSW-US



WOCT-US



F-WOCT-US



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2 3/4 in. deep - non-gangable - 3 3/4 in. high – device boxes						
WSW-US	18.0	2 1/4	–	–	4	Nonmetallic sheathed cable
F-WSW-US	18.0	2 1/4	–	–	4	Nonmetallic sheathed cable
2WSW-US	33.0	4	5	5 1/2	8	Nonmetallic sheathed cable
2-FWSW-US	33.0	4	5	5 1/2	8	Nonmetallic sheathed cable
2 3/4 in. deep - 3 3/4 in. high – 4 in. wide – ceiling boxes						
WOCT-US	26.0	–	–	–	4	Nonmetallic sheathed cable
F-WOCT-US	26.0	–	–	–	4	Nonmetallic sheathed cable