Red Dot Weatherproof kits

Metallic and nonmetallic

Metallic single-gang universal GFCI receptacle kit with "Extra-Duty" while-in-use cover, weather- and tamper-resistant, horizontal or vertical

Cat. no.	Colour	Description	Std. ctn.
S355E-CN	Grey box with grey cover	Metallic box with three ½ in. hubs, 17.3 cu. in., metallic cover, ground screw, vertical only	4
S355P-CN	Grey box with clear cover	Metallic box with three ½ in. hubs, 17.3 cu. in., nonmetallic cover, ground screw	4

Nonmetallic "Extra-Duty" while-in-use kits with GFCI receptacle

Cat. no.	Colour	Description	Std. ctn.
CKPS-C-CN-KIT	Grey box with clear cover	Box and while-in-use cover kit. Single-gang device box, 2 in. deep, 3 hubs ½ in. Grey with mounting lugs, two closure plugs and ground screw. Single-gang while-in-use extra duty shallow cover, 2¼ in. Deep clear, nonmetallic and GFCI receptacle.	4
CKPS-W-CN-KIT	White box with white cover	Box and while-in-use cover kit. Single-gang device box, 2 in. deep, 3 hubs ½ in. White with mounting lugs, two closure plugs and ground screw. Single-gang while-in-use extra duty shallow cover, 2¼ in. deep, white, nonmetallic and GFCI receptacle.	4
CKPM-W-CN-KIT	White box with white cover	Box and while-in-use cover kit. Single-gang device box, 2 in. deep, 3 hubs ½ in. White with mounting lugs, two closure plugs and ground screw. Single-gang while-in-use extra duty medium cover, 2½ in. deep, white, nonmetallic and GFCI receptacle.	4
CKPS-BR-CN-KIT	Bronze box with bronze cover	Box and while-in-use cover kit. Single-gang device box, 2 in. deep, 3 hubs ½ in. Bronze with mounting lugs, two closure plugs and ground screw. Single-gang while-in-use extra duty shallow cover, 2¼ in. deep, bronze, nonmetallic and GFCI receptacle.	4
CKPM-BR-CN-KIT	Bronze box with bronze cover	Box and while-in-use cover kit. Single-gang device box, 2 in. deep, 3 hubs ½ in. Bronze with mounting lugs, two closure plugs and ground screw. Single-gang while-in-use extra duty medium cover, 2% in. deep, bronze, nonmetallic and GFCI receptacle.	4



Metallic and nonmetallic

_

Cat. no.	Colour	Description	Std. ctn.
CKPS-C-CN-PKIT	Grey box with clear cover	Box and while-in-use cover kit. Single-gang device PVC box grey, 3 threaded hubs ½ in. with ground screw. Single-gang while-in-use extra duty shallow cover, 2¼ in. deep clear, nonmetallic and GFCI receptacle.	4
CKPS-W-CN-PKIT	White box with white cover	Box and while-in-use cover kit. Single-gang device PVC box white, 3 threaded hubs ½ in. with ground screw. Single-gang while-in-use extra duty shallow cover, 2¼ in. deep white, nonmetallic and GFCI receptacle.	4
CKPM-C-CN-PKIT	Grey box with clear cover	Box and while-in-use cover kit. Single-gang device PVC box grey, 3 threaded hubs ½ in. with ground screw. Single-gang while-in-use extra duty medium cover, 2‰ in. deep clear, nonmetallic and GFCI receptacle.	4
CKPM-W-CN-PKIT	White box with white cover	Box and while-in-use cover kit. Single-gang device PVC box white, 3 threaded hubs ½ in. with ground screw. Single-gang while-in-use extra duty medium cover, 2% in. deep white, nonmetallic and GFCI receptacle.	4
CKPL-C-CN-PKIT	Grey box with clear cover	Box and while-in-use cover kit. Single-gang device PVC box, grey, 3 threaded hubs ½ in. with ground screw. Single-gang while-in-use extra duty large cover, 4¼ in. deep, clear, nonmetallic and GFCI receptacle.	3

Nonmetallic "Extra-Duty" while-in-use kits with GFCI receptacle (continued)