


WIRE GUARDS & MOUNTING SHELVES

EXIT SIGNS

PART #	MOUNTING	SIGNS		DIMENSIONS		
				W	H	D
460.0027-RL	End Mount	TUF RA RT	NEXTN RN RS RP ULT RX	10-1/2" (26.7 cm)	6" (15.2 cm)	16" (40.6 cm)
460.0028-RL	Ceiling Mount	TUF RT RA RP	NEXTN RN RS ULT	14-1/2" (36.8 cm)	6-1/4" (15.9 cm)	10-1/2" (26.5 cm)
460.0048-RL	End Mount		CNESTU	10-1/2" (26.7 cm)	6" (15.2 cm)	21" (53.3 cm)
460.0057-RL	Wall Mount		CNESTU	20-3/4" (52.7 cm)	10" (25.4 cm)	4" (10.2cm)
460.0058-RL	Ceiling Mount		CNESTU	21-3/4" (55.2 cm)	5-1/2" (14 cm)	10-1/2" (26.7cm)
460.0059-RL	Wall Mount	CNEXTN	CNSXTN	31" (86.4 cm)	10" (25.4 cm)	4-1/2" (14 cm)
460.0060-RL	End Mount	N-TUF RNC RSC	RAC SM-NEXTN	20" (50.8 cm)	12" (30.5 cm)	15" (38.1 cm)
460.0060-RL	Ceiling Mount	RNC SM-NEXTN RAC RSC	R-SN ULT Combo N-TUF RH TUF-HZ	20" (50.8 cm)	12" (30.5 cm)	15" (38.1 cm)
460.0078-RL	Wall Mount	N-TUF RHC HZ	RNC Ultima™ Combo	18" (45.7 cm)	18" (45.7 cm)	7" (17.8 cm)
460.0079-RL	Wall Mount	TUF RT RP RA	NEXTN Ultima™ Exit RN RS ULTD	14-1/4" (36.2 cm)	9-7/8" (25.0 cm)	4-5/8" (11.7 cm)
460.0080-RL	Wall Mount	SM-NEXTN RH	TUFHZ RSC RAC	15-1/4" (38.7 cm)	14-1/8" (35.9 cm)	6-1/2" (16.5 cm)
460.0081-RL	Wall Mount		R-SN	20" (50.8 cm)	17-1/8" (43.6 cm)	8-1/2" (21.6 cm)



WIRE GUARDS & MOUNTING SHELVES

BATTERY UNITS

PART	MOUNTING	COMMERCIAL, DECO UNIT	DIMENSIONS		
			W	H	D
460.0078-RL	Wall Mount	"A" Cabinet-6V, 12V, 24V-Max. 144W	17" (45.7 cm)	17" (45.7 cm)	7" (17.8 cm)
460.0081-RL	Wall Mount	"B" Cabinet-6V-180W 12V-216 to 360W 24V-200 to 288W	20" (50.8 cm)	17-1/8" (43.6 cm)	8-1/2" (21.6 cm)
460.0034-RL	Wall Mount	"C" Cabinet 24V-350 to 720W	28-1/8" (71.5 cm)	21-1/8" (53.7 cm)	10" (25.4 cm)
460.0097-RL	Wall or Ceiling Mount	LDX-VQ	31"(53.3 cm)	7"(17.8 cm)	6"(15.2 cm)
460.0080-RL	Wall Mount	LDXC, LDXA, Ultima	15-1/4" (38.7 cm)	14-1/8" (35.9 cm)	6-1/2" (16.5 cm)
460.0105-RL	Ceiling Mount	IPR 48"	54.6' (138.68 cm)	8' (20.32 cm)	5' (12.7 cm)

REMOTE HEADS

PART #	REMOTE HEADS	DIMENSIONS		
		W	H	D
460.0029-RL	TUF-NM, RM, VQ, RL40M	8-1/4" (21.5 cm)	6-1/4" (15.9 cm)	6-3/4" (17.2 cm)
460.0031-RL	VQW	25-1/4" (64.1 cm)	8-1/2" (21.5 cm)	8-1/2" (21.5 cm)
460.0032-RL	VQ2, RL150D	9-1/2" (24.1 cm)	9-1/2" (24.1 cm)	6-1/8" (15.6 cm)
460.0082-RL	Guardian™, Cadilite™	12"(30.5 cm)	9"(22.9 cm)	9"(22.9 cm)
460.0078-RL	Triple Remote	17"(45.7 cm)	17"(45.7 cm)	7"(17.8 cm)

MOUNTING SHELVES

