

New product

ESC-BLD Series

Steel combination unit




Features

- “Built-in” 3W LED heads
- Universal mounting: end, wall or ceiling
- Meets or exceeds CSA 22.2 No.141-15 standard for unit equipment and pictogram signs
- Sealed, maintenance-free, 6V lead-calcium battery
- **Warranty details at: www.emergi-lite.ca**

Dimensions

Dimensions are approximate and subject to change.



Typical specifications

Supply and install **Emergi-Lite® ESC-BLD Series** combination emergency light battery unit and pictogram sign. The unit shall be made of solid steel sheet metal and be suitable for universal mounting: wall, end, or ceiling. The legend housing shall have a maximum depth of 2-1/8". The legend faceplate(s) shall be constructed of robust clear polycarbonate panel(s) with an opaque border coloured factory-white. The light source shall be white light-emitting diodes (LED) and shall provide even illumination in normal and emergency operation. The power pack shall include one circuit board with test switch and pilot light for battery charger and legend LED driver. The unit shall include one 6V, maintenance-free, sealed lead-calcium battery and shall provide minimum 30 minutes of emergency lighting upon AC power failure. The electrical power available for emergency lights shall be 24W.

The equipment shall meet or exceed the requirements of CSA 22.2 No.141-15 standard.

The equipment shall be **Emergi-Lite®** model: _____.

Wire guards

Ordering code	Description
460.0081-E	Wall mount
460.0060-E	Ceiling mount

Power consumption and unit rating

Model	AC specs	Emergency power available for lamps				
		30 min	1H00	1H30	2H00	4H00
Pictogram module	120/347VAC	Less than 1.5W	-	-	-	-
ESC24		0.13/0.05 A	24	14	10	8

Ordering information

Series	Voltage/capacity	Colour	Heads	Head style & power	Options
ESC= pictogram steel combo sign	24= 6V-24W	W= factory white	1= one head 2= two heads	BLD= built-in LED	-2= 120/277VAC input DF= double face sign

Example: ESC24W2BLD

EMERGI-LITE