



PL27 Series

200 A 600 V; polyphase

Product specifications

- Conductor range: 6 AWG–250 kcmil
  - Tunnel type connector for both load and line sides
  - For overhead and combination overhead/underground service
  - Larger hub opening requires use of 3 in., 3½ in. or 4 in. hubs unless BS052 adapter plate is used
- Supplied with screw type ring
  - Weatherproof Type 3R enclosure



|  | Cat. no.     | Description   | Dimensions (in.)               |    |                                | Weight each |     |
|--|--------------|---|--------------------------------|----|--------------------------------|-------------|-----|
|  |              |   | H                              | W  | D                              | lb          | kg  |
|  | <b>7 Jaw</b> |   |                                |    |                                |             |     |
|  | PL27-V       | Overhead hub opening                                | 20 <sup>7</sup> / <sub>8</sub> | 12 | 5 <sup>7</sup> / <sub>16</sub> | 18          | 8.1 |
|  | PL27-TCV     | Combination overhead-underground                    | 20 <sup>7</sup> / <sub>8</sub> | 12 | 5 <sup>7</sup> / <sub>16</sub> | 18          | 8.1 |
|  | PL27-INV     | Overhead hub opening, insulated neutral             | 20 <sup>7</sup> / <sub>8</sub> | 12 | 5 <sup>7</sup> / <sub>16</sub> | 18          | 8.1 |
|  | PL27-INTCV   | Combination overhead-underground, insulated neutral | 20 <sup>7</sup> / <sub>8</sub> | 12 | 5 <sup>7</sup> / <sub>16</sub> | 18          | 8.1 |

Diagrams

