

BE1 Series


125 A 600 V; king size



Product specifications

- Conductor range: 6–1/0 AWG
Neutral Conductor Range: 1/0–14 AWG
Ground Conductor range: 2–14 AWG
- Aluminum tunnel type connectors for both load and line sides

- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	4 Jaw						
	BE1-V	Overhead, hub opening	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-INV	Overhead, hub opening, comes with isolated neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-1 1/4V	Overhead, hub opening, comes with 1 1/4 in. hub	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-1 1/4INV	Overhead, hub opening comes with 1 1/4" hub and isolated neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-1 1/4VGN	Overhead, comes with 1 1/4 in. hub and ground lug on neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-1 1/2V	Overhead, hub opening, comes with 1 1/2 in. hub	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-TV	Underground	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-INTV	Underground comes with isolated neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-TCV	Combination overhead-underground	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-TCVGN	Combination overhead-underground, comes with ground lug on neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-TCV-CR	Combination overhead-underground, corrosion resistant	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-TCVGN-CR	Combination overhead-underground, comes with ground lug on neutral, corrosion resistant	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-INTCV	Combination overhead-underground comes with isolated neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE1-5-TVGN	Combination overhead-underground	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE11-V-CM	Overhead, twin hub opening	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE11-1 1/4V	Overhead, twin hub opening comes with 1 1/4 in. hubs	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE11-1 1/4INV	Overhead, twin hub opening comes with 1 1/4 in. hubs and isolated neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	BE11-1-1/4 VGN	Overhead, twin hub opening, comes with 1 1/4 in. hubs and ground lug on neutral	14 ¹¹ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
	Factory-installed accessories						
Include: -5			5 th jaw, standard capacity, 9 o'clock position				

Diagrams

