Copper colloidal surface treatment protects, lubricates and enhances conductivity of all electrical connections



- Unique, homogenized blend of pure, polished colloidal copper, rust and corrosion inhibitors
- Simultaneously protects, lubricates and enhances conductivity of mating surfaces
- Extremely adhesive compound flows smoothly into uneven contours and voids, ensuring easy application and complete, positive protection and lubrication
- Won't settle out, thin, thicken, harden or dry out under the most severe environmental conditions
- Excellent temperature characteristics- can be brushed on at -45.5 °C (-50 °F) to 121 °C (250 °F) (other compounds either turn solid or run like water at these extremes) and remains intact at short terms even at 980 °C (1,800 °F)

Good connections are one of the most important aspects of electrical work. Mechanics know how much downtime is caused when fluids or oils leak into the raceway system or when they have to look for a weak link in a ground system caused by a high-resistance connection. Mechanics also know how much time is spent keeping contacts, switches, lugs and other connectors clean or replacing parts because of "green scourge" buildup. ABB has the solution to improve connections made in thousands of electrical and raceway installations made each day by electricians everywhere. Kopr-Shield® compound may be used to advantage in all electrical installations. When the environment is hostile to electrical and mechanical connections, Kopr-Shield compound is a must.

Use Kopr-Shield compound for battery lugs and cables to:

- Prevent "green scourge" corrosion
- Reduce resistance
- Ease terminal installation and removal

Use Kopr-Shield compound for raceways to:

- Lubricate for ease of assembly and disassembly
- Improve grounding continuity (exceeds code requirements)

Use Kopr-Shield compound for fuse clips to:

- Eliminate hot spots for even heat distribution
- Prevent oxidation by preventing carbon path formation
- Lubricate for easy installation and removal of fuses

Use Kopr-Shield compound for wiping contacts, drum switches and slip rings to:

- Prevent galling, burning, pitting and discoloration
- Suppress arcing and dissipation of coronas
- Lubricate for ease of operation

Kopr-Shield joint compound

Cat. no.	Description	Std. pkg.	Weight lb/C
201-31879	1½-oz. Container with brush	96	11.46
201-31879-1	4-oz. Container with brush	24	38.54
СР8-ТВ	8-oz. Container with brush	12	64.58
CP16	16-oz. Container with brush	12	120.83
CP128	1-Gallon can	4	952.00



Cat. no. Contains Description 21059 1-pt. Squeeze bottle For aluminum cable connections; contains fine zinc particles which break through oxide film on cable strands upon compression of connection; ensures a low resistance contact and seals out air and moisture. M53 5-Gallon can



Belleville compression washers

- Essential when bolting aluminum lugs and connectors to bus bars with steel or brass hardware
- Maintain constant pressure in heavy-duty, high-temperature applications
- Available with or without flat washer

When bolting aluminum lugs and connectors to bus bars with steel or brass hardware, the recommended practice to ensure a tight connection is to use a Belleville spring washer on top of a flat washer under the bolt head or nut. For heavy-duty service where the heat rise is expected to exceed 30 °C above ambient, this procedure maintains constant pressure as the connector metals expand and contract with temperature changes.

Belleville compression washers

				D	imensions in. (mm)
			Flat washer		Belleville washer
Cat. no.	Bolt size (in.)	0.D.	Thickness	0.D.	Thickness
Belleville compres	ssion washers plus flat washer				
60800B	1/4	0.75 (19.1)	0.07 (1.8)	0.69 (17.5)	0.06 (1.5)
60801B	5⁄16	0.88 (22.1)	0.07 (1.8)	0.81 (20.6)	0.07 (1.8)
60802B	3∕8	1.00 (25.4)	0.08 (2.0)	0.94 (23.9)	0.08 (2.0)
60803B	¹ /2	1.25 (31.8)	0.11 (2.8)	0.81 (20.6)	0.10 (2.5)
Belleville compres	ssion washer only				
60800	1/4	-	_	0.69 (17.5)	0.06 (1.5)
60801	⁵ ⁄16	-	-	0.81 (20.6)	0.07 (1.8)
60802	3∕8	-	-	0.94 (23.9)	0.08 (2.0)
60803	¹ /2	-	-	0.81 (20.6)	0.10 (2.5)
60804	5⁄/8	-	_	1.50 (38.1)	0.11 (2.8)

Diagram



Note: Ordering quantity must be in unit quantities and multiples thereof.

The Belleville washer should be installed with a larger flat washer to spread the high stresses of the compression washer edges over a large area of the lug and/or bus bar.



Dragon Tooth® transition washers

Quick, dependable and versatile.

- Connect copper-to-aluminum, copper-to-copper or aluminum-to-aluminum components
- Toothed surface penetrates aluminum and copper oxides
- Lower installed cost no need to grind aluminum surfaces, apply compounds or use spring-type washers

Dragon Tooth transition washers

Cat. no.	Size (in.)	Bolt torque (inlb)
DTW14	1/4	50-80
DTW516	5⁄16	125–160
DTW38	3/8	160–240
DTW12	1/2	390–540
DTW58	5/8	540-730







Hex head	bolts	and	nuts
----------	-------	-----	------

Cat. no. Diameter and threads per inch			Length	
¼ in20	⁵⁄16 in.–18	³⁄₃ in.–16	½ in.–13	(in.)
Type BB — Silicon	bronze hex head bolts			
25100BB-C	31100BB-C	37100BB-C	50100BB-C	1
-	31125BB-C	37125BB-C	50125BB-C	11/4
-	31150BB-C	37150BB-C	50150BB-C	11/2
_	31175BB-C	37175BB-C	50175BB-C	13/4
_	31200BB-C	37200BB-C	50200BB-C	2
25225BB-C	31225BB-C	37225BB-C	50225BB-C	21/4
-	31250BB-C	37250BB-C	50250BB-C	21/2
-	31275BB-C	37275BB-C	50275BB-C	23/4
_	31300BB-C	37300BB-C	50300BB-C	3
_	_	37325BB-C	50325BB-C	31/4
-	_	37350BB-C	50350BB-C	31⁄2
Type HN — Silicon	bronze hex nuts			
14010HN-C	31010HN-C	37010HN-C	50010HN-C	-

Washers

Cat. No.	Bolt size (in.)	O.D. (in.)	I.D. (in.)	Thickness (in.)	Height (in.)
Type SW — Silio	on bronze split lock	washers			
14030SW-C	1/4	-	-	_	-
31030SW-C	5/16	-	_	-	-
37030SW-C	3/8	-	_	-	-
50030SW-C	1/2	-	-	-	-
Type FW — Silio	on bronze flat wash	ers			
14040FW-C	1/4	1/4	11/16	0.260	0.040
31040FW-C	5/16	5/16	7/8	0.336	0.064
37040FW-C	3/8	3/8	1	0.395	0.064
50040FW-C	1/2	1/2	11/4	0.562	0.091
Type BW – Belle	ville compression w	asher 304 serie	s stainless st	eel	
50050BW-C	1/2	11/8	17/32	0.062	1/8

Sealants and lubricants



Type CT — CONTAX[™]

- oxide inhibiting compound
- Seals electrical connections from oxygen and moisture
- Non-water soluble, non-petroleum based polymer grease
- Nontoxic, will not irritate the skin
- Service temperature to 238 °C (460 °F); can be applied in -18 °C (0 °F) weather

Cat. no.	Description
СТА	½ oz. Package
СТВ	4 oz. Plastic bottle
СТВ8	8 oz. Plastic bottle
СТQ	Quart can
CTG	Gallon can



Silicone lubricant for high voltage electrical work

Cat. No.	Description	Pkg. qty.
2012	2 grams	250 tubes
2015	5 grams	100 tubes
SL5	5 oz./142 grams	12 tubes



Type DX — Duct seal

- Seals around junction boxes, flashings, service mast entries, service cable entries and countless other applications
- Easy to use, forms around irregular surfaces and configurations
- Highly resistant to cracking, drying and shrinking
- Cuts and trims easily
- Can be painted immediately after application
- Grey colour
- No unpleasant odor
- -6.7 °C to 100 °C (20 °F to 212 °F) workable temperature range
- -40 °C to 121 °C (-40 °F to 250 °F) service temperature range
- Contains no asbestos

Cat. no.	Description
DX-1	1 lb Slug
DX-5	(5) 1 lb Slugs
DX-5S	5 lb Slug



Cat. No.	Description	Pkg. qty.
WWB1	Complete brush with handle	1
WRB1	Brush replacement	1

(VĽ