

Mini-Inverter Series

Interruptible unit equipment



Features

The **Mini-Inverter** is a cUL Listed stand-alone pure sine wave output inverter designed to provide power to designated emergency lighting fixtures. In a power loss situation, it will supply power from the onboard battery supply. The **Mini-Inverter** works in conjunction with incandescent, LED, and fluorescent fixture types and will automatically run switched, normally-on, or normally-off designated emergency fixtures. The **Mini-Inverter** is ideal for applications requiring an emergency source for lighting arrangements that utilize multiple lamp and fixture types and is available in surface mount and comes with a one-year warranty and nine-year pro-rata battery warranty.

- Lamps operated: Incandescent LED, fluorescent lamps and ballast combinations, including TRIAC dimmable ballasts
- Components: High-efficiency pure sine wave inverter
- Temperature-compensated charger 12V oversized Valve Regulated lead acid (VRLA) battery
- Construction: 18-gauge steel for 300W & 600W/ 14-gauge steel for 1000W & 1440W with a white baked-on powder coat paint finish
- Emergency lighting supplied from one convenient, reliable source
- Input/output voltage 120/120V 60Hz or 347/347V 60 Hz
- Replaceable output fuse protection
- Valve regulated lead acid (VRLA) battery provides long-life and is maintenance free
- Line voltage allows for remote mounting of emergency fixtures at distances up to 1000 feet
- Low battery voltage disconnect
- Unit comes standard with electronic lockout and brownout circuits
- Meets or exceeds all National Electrical Code and Life Safety Code Emergency Lighting Requirements
- Cabinet in factory white powder-coat paint finish
- **May accept load to 80% capacity when load feature power factor of 0.9 or more**
- Non audible auto-diagnostic is standard. Nexus® system interface available with an improved minimum lost load detection of 10%.
- Standard lighting control override for 0-10V dimming systems
- Meets or exceeds the requirements of CSA 141-15
- Consult your sales for high bay/after market LED lamp applications

Typical specifications

Emergency lighting shall be provided by inverter unit equipment designed to operate designated incandescent, fluorescent and LED fixtures on emergency power at their full nominal lumen rating during the full 30 minute emergency discharge cycle. System output will be rated at watts for 30 minutes and provide fused output connections to the load. The system's voltage rating shall be VAC input/output nominal. The inverter unit shall allow for fused connected emergency fixture(s) to be normally on, normally off, switched or dimmed without affecting lamp operation during a power failure.

Upon utility power loss, the inverter unit shall deliver 100% of its rated output to the emergency fixtures regardless of the local switch or dimmer (TRIAC) position, and will provide power to emergency fixtures at distances of up to 1000 feet. The housing shall be manufactured using 18-gauge steel for 300W & 600W/ 14-gauge steel for 1000W & 1440W with a white baked-on powder coat paint finish. The unit's electronics shall include a self-contained inverter section with a fully automatic, thermalcompensating variable-rate battery charger, AC lockout feature, low battery voltage disconnect, overload, short circuit and brownout protection as standard. The unit shall utilize a sealed lead acid battery with a 10-year design life. The inverter system shall be cUL Listed and labeled. The unit shall be covered under a 1-year warranty on the electronics and battery and a 9-year pro-rata warranty on the battery. It shall meet or exceed the requirements of CSA 141-15.

Specifications

Transfer time: 400W-268ms, 600W-264ms,
1000W-540ms, 1440W-510ms

Voltage regulation on emergency: + 3%

Frequency regulation on emergency: 60 Hz +/- 1%

Load power factor range: 0.9 leading to 0.9 lagging

Operating temperature: 20° to 30°C (68° to 86°F)

Warranty

All **Emergi-Lite®** inverter products receive 100% quality inspection before shipment to insure proper and satisfactory operation. When operated under normal conditions, **Emergi-Lite®** inverter products will provide years of dependable service. This unit is backed by a complete 1-year warranty against defects in material or workmanship, and a 9-year prorata battery warranty.

Warranty details at: www.emerigi-lite.ca


The inverter unit is **Emergi-Lite®** model: _____ .

nexus Nexus®Pro c 

Mini-Inverter Series

Interruptible unit equipment

Wiring diagram



Electrical characteristics & dimensions

Power rating	Max. input rating		Sine wave	Installation	Cabinet dimensions			No. of batteries	Weight		Weight w/o battery	
	120VAC	347VAC			W"	H"	D"		120V	347V	120V	347V
300W	3.10	N/A	Pure	Wall	27"	12.25"	7.25"	1	55 lbs	N/A	30 lbs	N/A
600W	6.00	2.30	Pure	Wall	24"	20.25"	10.5"	2	105 lbs	117 lbs	55 lbs	67 lbs
1000W	11.60	3.60	Pure	Wall	24"	20.25"	14.5"	2	150 lbs	169 lbs	70 lbs	89 lbs
1000W/60	14.00	N/A	Pure	Wall	24"	40.75"	14.5"	4	320 lbs	N/A	198 lbs	N/A
1440W	15.00	5.00	Pure	Wall	24"	20.25"	14.5"	2	190 lbs	214 lbs	75 lbs	99 lbs

Power consumption and unit rating

Model number	AC specs	Emergency power available for load					
		30 min	1H00	1H30	2H00	4H00	
EMI-300	120VAC	3.10 Amps	300W	175W	125W	100W	50W
EMI-600	120 / 347VAC	6.00 / 2.30 Amps	600W	350W	250W	200W	100W
EMI-1000		11.60 / 3.60 Amps	1000W	585W	415W	330W	165W
EMI-1000/60	120VAC	14.00 Amps	1000W	1000W	1000W	778W	473W
EMI-1440	120 / 347VAC	15.00 / 5.00 Amps	1440W	842W	600W	480W	240W

Ordering information

Series	Capacity	Voltages in/out	Diagnostic features	Options
EMI= Series	-300= 300W -600= 600W -1000= 1000W -1000/60= 1000W ¹ -1440= 1440W	-1= 120/120VAC, 60 Hz -3= 347/347VAC, 60 Hz ¹	Blank= Auto-Diagnostics, non-audible ¹ -U= Auto-Diagnostics, audible ¹ -NU= no Diagnostics -NEX= Nexus® wired system interface ² -NEXP= Nexus®Pro IoT ² -NEXRF= Nexus® wireless system interface ²	-4= four output circuits ¹ -D3= time delay (15 minutes) -LC= line cord (120V only) -LW= cord and twist lock plug (120V only) -SAC= service alarm contact

¹Available only with "-4" option

¹Available only with 600W, 1000W & 1440W

¹Minimum load required: 10% of unit capacity
²Please consult your sales representative

¹1000W/60 model at 120V only

Example: EMI-1440-1