New product

ELFT Single Phase Series

Fast transfer emergency lighting inverter system 1.5KVA –16.7KVA



Features

- 98% efficient at full load
- 2ms transfer time
- PWM/IGBT technology
- Self-testing/Self-diagnostic
- User programmable with password protection
- Standard input circuit breaker
- RS232 communication port
- Micro-processor controlled
- 30 min. standard run time
- Generator compatibility
- Custom and mixed voltages available
- Automatic event, test and alarm log
- Space saving single cabinet design
- Maintenance free standard batteries
- Forced air cooling during emergency mode only
- cUL Listed to CSA 22.2.141-15. Meets NFPA101



ELFT Series 30 minute run time

			Cabinet dimensions (cm)			ensions (cm)	Batteries		Total		
Partial model number	Power rating (kW) 30 min.	Voltage in-out VAC	W (cm)	H (cm)	D (cm)	Weight (kg)	No. of batteries	Weight (kg)	system weight (kg)	Total no. of cabinets	347V XFM cabinet
1	1.50	120 or 277	76-	119	64	98	4	66	164	1	
1	1.50	347	70	175	04	154	4	00	220	1	Top cabinet
2	2.25	120 or 277	76-	119	64	104	6	99-	203	1	
	2.25	347	70	175	04	161	0	33	260	1	Top cabinet
3	3.00	120 or 277	76-	119	64	107	8	132	239	1	
3	3.00	347	70	175	04	166	0	132	298	1	Top cabinet
4	3.75	120 or 277	76-	119	64	109	10	165-	274	1	
4	3.75	347	76	175		171	10	105	336	1	Top cabinet
5	5.00	120 or 277	76-	119	64	127	12	198	325	1	
5		347	76	175		193	12	190	391	1	Top cabinet
	6.00	120 or 277	122	193	64	274	1.5	240	522	1	
6		347	198			356	15	248	603	2	Side cabinet
7	8.00	120 or 277	122	400	C 4	290	20	220	621	1	
7		347	198	193	64	377	20	330-	708	2	Side cabinet
	10.0	120 or 277	122	400		356	4.0	200	746	1	
8		347	198	193	64	449	12	390-	839	2	Side cabinet
	12.5	120 or 277	122	400		365		400	853	1	
9		347	198	193	64	465	15	488	953	2	Side cabinet
	167	120 or 277	122	100	.	401	22	650	1052	1	
10	16.7	347	198	193	64	508	20	650-	1158	2	Side cabinet

ELFT Single Phase Series

Fast transfer emergency lighting inverter system 1.5KVA –16.7KVA


ELFT Series 60, 90 & 120 minute run time


	Powe	r rating	(kW)		Cabinet dimensions (cm) ¹				Batteries		Total			
Partial model number	60 min.	90 min.	120 min.	Voltage in-out VAC	W (cm)	H (cm)	D (cm)	Weight (kg)	No. of batteries	Weight (kg)	system weight (kg)	Total no. of cabinets	347V XFM cabinet	
1	1.50	1.39	1.28-	120 or 277	76-	119	64	98	4	130-	228	1		
1	1.50	1.39	1.28	347	76-	175	64	154	4	130	284	1	Top cabinet	
2	2.25	2.08	1.91	120 or 277	76-	119	64	104	_	195	299	1		
2	2.25	2.08	1.91	347	76-	175	64	161	6	195	356	1	Top cabinet	
2	2.00	2.70	2.55	120 or 277	76	119	64	107	8	260	367	1		
3	3.00	2.18	2.78	2.55	347	76-	175	64	166	8	260	426	1	Top cabinet
4	3.75	3.47	7 3.19	120 or 277	76-	119	64	109	10	325	434	1		
4	3.75			347	347 175	171	10 325	325	496	1	Top cabinet			
_	F 00	4.63	4.25	120 or 277	20 or 277 76—119 64—127	200	517	1						
5	5.00	4.03	4.23	347	76-	175	64	193	12	390	583	1	Top cabinet	
_	6.00	5.55	5.10	120 or 277	122	193	64	274	15	488	762	1		
6				347	198	193	64	356	15	488	843	2	Side cabinet	
7		7.40	6.00	120 or 277	122	100	6.4	290	20	650	941	1		
7	8.00	7.40	6.80	347	198	193	64	377	20	650	1028	2	Side cabinet	
				0.50	120 or 277	122	100	6.4	356	24	701	1137	1	
8	10.0	9.25	8.50	347	198	193	64	449	24	781	1230	2	Side cabinet	
0	12.5	11.6	10.0	120 or 277	122	102	64	365	20	076	1341	1		
9	12.5	11.6	11.6	10.6	347	198	193	64	465	30	976	1441	2	Side cabinet
10	167	15.4	112	120 or 277	122	100	6.4	401	40	1201	1702	1		
10	16.7	15.4	14.2	347	198	193	64	508	40	1301	1809	2	Side cabinet	

 $^{{}^{\}scriptscriptstyle 1}\!\mathsf{The}$ cabinet dimensions above include the side cabinet

— Dimensions

Dimensions are approximate and subject to change.





ELFT Single Phase Series

System specifications


System specifications

General	
Design	Standby PWM inverter type utilizing IGBT technology with 2ms transfer time
Control	Microprocessor controlled, 4 x 20-character display with touch pad controls & functions Continuous scrolling display of system status and faults, with alarm feature
Metering	Input and output voltage, battery voltage, battery and output current, output VA, temperature, inverter wattage
Communication	RS-232 port (DB9)

Electrical input	
Voltage	120, 208, 240, 277 or 347VAC 1-phase 2-wire +10% - 20%. Contact factory for all other voltages
Input power walk-in	Limiting inrush current to less than 125%, 10 times for 1 line cycle
Input frequency	60Hz, +/-3%
Protection	Input circuit breaker
Harmonic distortion	<10%
Power factor	0.5 lag/lead

Electrical output							
Voltage	120, 208, 240, 277 or 347VAC, 1-phase 2-wire Contact factory for all other voltages						
Static voltage	Load current change +/-4%, battery discharge +/-12.5%						
Dynamic voltage	+/- 2% for a +/- 25% load step change +/- 3% for a 50% load step change, recovery within 10 cycles						
Harmonic distortion	<3% THD for linear load						
Output frequency	60Hz +/- 0.05Hz during emergency mode						
Load power factor	0.5 lag to 0.5 lead						
Overload capability	100% for continuous rating, 115% for 10 minutes, 150% for 16 cycles						
Protection	Optional distribution circuit breaker						
Crest factor	2.8						

Environmental c	Environmental conditions							
Storage/transport	 -4°F to 158°F (-20°C to 70°C) without batteries max. 3 months at 104° F (40° C) -0°F to 104°F (-18°C to 40°C) with batteries 							
Operating temperature	System operates safely from 32°F to 104°F (0°C to 40°C) but optimum operation is between 68°F and 86°F (20°C to 30°C). Battery performance can be affected by temperature							
Altitude	<10,000 feet (above sea level) without de-rating							
Relative humidity	0 to 95% non-condensing							
Audible noise	50 dBA at 1m from surface in emergency mode							



ELFT Single Phase Series

System specifications and ordering information

Cabinets

Modular design, freestanding NEMA type 1 steel cabinets powder coated for corrosion and scratch resistance. Front access design through hinged lockable doors requires only 39" front clearance and 12" top clearance. Cabinets are stackable up to 16.7kVA, if required to further reduce the footprint. Top and left side conduit entry with knockouts up to 16.7kVA. Left side only for 24kVA and up.

Inverter

Using IGBT/PWM technology the inverter converts the DC voltage supplied by the batteries to AC voltage of a precise stabilized amplitude and frequency, suitable for most sophisticated electrical equipment. True sinusoidal output waveform with very low distortion (less than 3% for linear loads). Overload capability of up to 150% for 16 line cycles.

Charger

Fully automatic, temperature compensated, microprocessor controlled charger recharges fully discharged batteries in maximum 24 hours at nominal AC input voltage. AC input current limiting and over-voltage protection included.

Battery

System is provided standard with 10 year, maintenance-free, sealed valve regulated, front terminals lead-calcium batteries. 30 min. standard discharge time at full load under normal operating temperature. Low voltage disconnect protection included. No special ventilation required.

Self-diagnostic

Automatic self-tests consist of a 5 minute monthly and full run time annual function. The front-mounted control panel includes 5 LED

indicators, a 4-line x 20-character OLED display, a keypad to control and monitor the internal operation of the system. This allows the operator to easily "watch" system functions as they occur and check on virtually any aspect of the system's operation. Standard RS232 diagnostic interface.

Alarms

High/low battery charger voltage, high/low AC input voltage, near low battery, low battery, load reduction fault, output overload, high ambient temperature, inverter fault, output fault, optional output circuit breaker trip.

Optional features

Output circuit breakers, output trip alarms, 12 hours fast recharge, internal/external maintenance bypass switch (BBM), remote summary alarm panel, summary alarm dry form C contact, inverter on dry contacts, normally-off output, bypass relays, seismic mounting, circuit breaker locks, battery temperature monitor, drip top, output transfer delay, time delay, zone monitoring, BACnet IP or MS/TP, remote meter panel, MODBUS TCP/IP or RTU, serial to ethernet adapter.

Factory start-up

Includes one additional year of warranty. See warranty conditions.

Warranty (Full limited warranty conditions available upon request) Limited manufacturer warranty is one year, parts and labor, for system electronics or two year with factory start-up program. Battery warranty is one year full plus 9 years pro-rata for a total of 10 years, under normal operating conditions. System must be put in service within 6 months from ship date in order to validate warranty.

How to order

Input/output voltage	Series	Nominal capacity	Battery type	Emergency run time	Output breaker configuration	Output breaker voltage	Output breaker amperage	Output breaker qty.
1= 120-120 2= 120-120/277 3= 208-120 ¹ 4= 240-120/240 5= 277-120 6= 277-277 7= 277-277/120 8= 208-120/240 ¹ 9= 347-347 A= 208-120/208 ¹ ¹ Enclosure height will increase on 1.5 to 5k/A units	ELFT	1= 1500VA 2= 2250VA 3= 3000VA 4= 3750VA 5= 5000VA 6= 6000VA 7= 8000VA 8= 10.0KVA 9= 12.5KVA 10= 16.7KVA	SG = Standard	R30= 30 minutes R60= 60 minutes R90= 90 minutes R120= 120 minutes	B= Normally ON N= Normally OFF ² ² Normally off loads cannot exceed 20% of total KVA rating with any combination of HID loads	A= 120 B= 208 C= 240 D= 277 Z= 347	10= 10 Amp 16= 16 Amp 20= 20 Amp 25= 25 Amp 32= 32 Amp 40= 40 Amp 50= 50 Amp 63= 63 Amp	01-24= Choose the number of output breakers between 01 and 24 ³

¹ Enclosure height will increase on 1.5 to 5kVA units		combination of HID loads		
Options		Monitoring	Warranty (one year standard)	Accessories
A= Remote summary alarm panel BL= Circuit breaker locks BTM= Battery temperature monitor C= Status monitoring contacts D= Drip top (NEMA 2) F= Battery charger upgrade (12 hours recharge) I= Inverter on dry form C contact L= Load control relay (line voltage dimmer or switch bypass) M(BBM)= Internal maintenance bypass	P= Remote status panel (status alarms, requires C option) R= Remote meter panel S= Summary fault form C contacts T= Output trip (supervised) alarm V= Time delay 15 minutes (15 minute retransfer time delay of normally off circuit after return of utility) Z= Seismic mounting (Anchorage based on calculations. For systems requiring OSHPD/Withstand testing, please contact the factory)	BAC= BACnet communication (MSTP) MOD= Modbus RTU BIP= BACnet IP MIP= Modbus TCP/IP SEA= Serial to ethernet adapter	2YW= Start up & same day training 2YT= Startup, same day training and full run test ⁴ 5YP= 5-year preventative maintenance plan (startup included) 5YW= 5-year extended electronics warranty TR= Training if required on day other than startup	Blank= No accessories EMBP= External maintenance bypass switch ⁵ SPARES= Spare fuses & circuit boards SPAREF= Spare fuse kit
Example: 2ELFT2SGR30BA1603BLBAC	ZM= Zone monitoring (quantity must be specified)		⁴ Load must be connected, additional day on-site required	⁵ Cannot be purchased with internal output breaker option

³Maximum output breakers available: 12 unsupervised (1-pole), 8 supervised (1-pole) for 1.5KVA-5KVA; 24 unsupervised (1-pole), 18 supervised (1-pole) for 6KVA-16.7KVA; Breakers provided are 20 Amps unless specified otherwise. A 2-pole breaker occupies 2 positions. Additional output breakers available on 1.5KVA units with optional top mount enclosure. Contact factory for details.