



## RCB-HO LED SERIES

Commercial Battery Unit

### TYPICAL SPECIFICATIONS


The contractor will install the **Ready-Lite® RCB-HO LED Series** battery unit. The emergency lighting system shall consist of fully automatic equipment with two High output LED heads. Each unit shall contain a fully automatic, solid state charger with test switch and AC ON pilot lights. The unit shall contain a sealed transfer circuit and low voltage disconnect circuit. The battery shall be 9.6V with a capacity of 12W for 90 minutes.

The unit shall be cUL approved to meet CSA 22.2 no. 141-15 standard.

The unit shall be **Ready-Lite®** model: \_\_\_\_\_ .

### DIMENSIONS

Dimensions are approximate and subject to change.



### FEATURES

- Fully adjustable LED glare-free lens
  - 5.4W long life high output LED light source
  - Provides 90° spacing at 7.5' mounting height
  - Dual voltage input capability 120/347VAC
  - Automatic, temperature compensated, pulse type charger
  - Low voltage disconnect prevents over discharge of battery
  - Automatic brownout protection
  - Sealed 9.6V-12W Lithium-ion battery offering 90 minutes of emergency lighting
  - Battery lock-out prevents discharge during installation
  - Red LED charger monitor
  - Momentary test switch allows for quick operational check
  - Injection-molded thermoplastic ABS housing
  - Rear keyhole slots and universal knock-outs to mount to any standard 4" junction box
  - Fast and easy installation with snap-together design
  - Ceiling or wall mount installation
  - Comes standard with one (1) year warranty
  - Meets or exceeds CSA C22.2 no.141-15
- See warranty details at: [www.tnb.ca/en/brands/ready-lite](http://www.tnb.ca/en/brands/ready-lite)

### POWER CONSUMPTION AND UNIT RATING

MODEL	AC SPECS			DC SPECS	
	Voltage	Current	Power	Battery Type	Runtime
RCB-HO	120/347VAC	0.08 A	0.8 W	LifePO	min. 90 minutes

### ORDERING INFORMATION

SERIES	VOLTAGE
RCB-HO= Commercial battery unit high output	Blank= 120/347VAC

EXAMPLE: RCB-HO