

RHPRL SERIES NEMA-4X Rated Remote Fixture

FEATURES

- PVC grey housing and heads designed for heavy-duty industrial applications: indoors, outdoors, hose-down areas, cold-storage facilities etc
- Can be installed in wide temperature conditions: -40°C to 55°C [40°F to 131°F]
- NEMA-4X protection grade against liquids and windblown dust
- High-efficacy LED emergency heads outperform traditional 50W incandescent lamps
- Innovative head design: four-LED and dual-driver provide illumination even in case of unexpected component failure
- Simple and easy to install on walls, poles, columns or struts. For vertical installation on poles or columns, use mounting bracket catalogue number: PMK1-R (sold seperately)
- Meet or exceed CSA C22.2 No.141-15-15
- 1 Year limited warranty See warranty details at: www.tnb.ca/en/brands/ready-lite

new product



TYPICAL SPECIFICATIONS


Supply and install the **Ready-Lite® RHPRL Series** remote emergency lighting fixtures. These remote fixtures will consist of either single or double lamp configurations. The housing shall be made of grey PVC, be designed for heavy duty industrial applications with temperatures ranging from -40°C to 55°C [40°F to 131°F]. The remote fixture can easily be installed on walls, poles, columns or struts. The heads shall be Die-Cast and have a flat square lens made of UV stabilized clear polycarbonate. Each head shall include four (4) high efficacy LEDS and two independent drivers.

The remote fixture shall fully adjustable without tools, be NEMA-4X rated and be cUL listed to CSA C22.2 No.141-15.

The remote unit shall be Ready-Lite® model: _

DIMENSIONS

Dimensions are approximate and subject to change.



*WARNING: Mounting column must be anchored at both ends: floor and ceiling.


PHOTOMETRY PERFORMANCE

Whether installed indoors or outdoors, the **RHPRL Series** of LED emergency lights deliver a stable and consistent illumination on the path of egress for a wide range of mounting heights. Depending on the application, one may select and specify among three levels of lumen output. See cross reference to traditional incandescent emergency lights below.

LED LAMP	POWER (W)	TOTAL LUMENS	OUTPERFORMS THE INCANDESCENT
L6	6W	565	35W PAR36, MR16 Halogen
L10	10W	1030	50W PAR36, MR16 Halogen
L15	15W	1320	50W MR16-IR Halogen

Industrial environment: wall mounted equipment, reflectances: 10/10/10; 6-ft wide illumination path. Illumination as per NBC; Average: 1fc; Min: 0.1fc.

MOUNTING HEIGHT	SPACING CENTRE-TO-CENTRE (FEET)			
	LAMP L6 / 6W, 565LM	LAMP L10 / 10W, 1000LM	LAMP L15 / 15W, 1300LM	
10 ft	80	110	140	
15 ft	70	105	135	
20 ft	60	100	130	
25 ft	50	95	120	



ORDERING INFORMATION

SERIES	NUMBER OF HEADS	LED HEAD
RHPRL= high performance remote	1= single 2= double	L6W= 12V, 24V-6W L10W= 12V, 24V-10W L15W= 12V, 24V-15W
		PMK1-R= pole mounting bracket (sold separately)

EXAMPLE: RHPRL2L10W

READY-LITE

