

## CO1 Multi-gang

200 A (main lugs), 100 A per position 120/240 V; multi-gang combination with or without breaker

CO12-100HI



Cat. no.	Type	Description	Position	Dimensions (in.)			Weight Each	
				H	W	D	lb	kg
<b>4 Jaw</b>								
CO12	Overhead	2 Gang, Provision for 2 X 2 pole 10 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-100	Overhead	2 Gang, Comes complete with 2 X 2 pole 100 A 10 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-100-U	Underground	2 Gang with blank compartment, comes complete with 2 x 2 pole 100 A 10 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-100HI	Overhead	2 Gang Comes complete with 2 X 2 pole 100 A 22 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-100HI-U	Underground	2 Gang with blank compartment, comes complete with 2 x 2 pole 100 A 22 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-SD	Overhead	2 Gang, Provision for 2 x Square D type QO 2 pole 10 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO12-SD-U	Underground	2 Gang with blank compartment, Provision for 2 x Square D type QO 2 pole 10 kA rated circuit breaker	2	23½	16½	4¾	30	13.60
CO13	Overhead	3 Gang, Provision for 3 X 2 pole 10 kA rated circuit breaker	3	23½	24¾	4¾	45	20.41
CO13-100	Overhead	3 Gang, Comes complete with 3 X 2 pole 100 A 10 kA rated circuit breaker	3	23½	24¾	4¾	45	20.41
CO13-100-U	Underground	3 Gang with blank compartment, comes complete with 3 x 2 pole 100 A 10 kA rated circuit breaker	3	23½	24¾	4¾	45	20.41
CO13-100HI	Overhead	3 Gang, Comes complete with 3 X 2 pole 100 A 22 kA rated circuit breaker	3	23½	24¾	4¾	45	20.41
CO13-100HI-U	Underground	3 Gang with blank compartment, comes complete with 3 x 2 pole 100 A 22 kA rated circuit breaker	3	23½	33½	4¾	45	20.41
CO13-SD	Overhead	3 Gang, Provision for 3 x Square D type QO 2 pole 10 kA rated circuit breaker	3	23½	33½	4¾	45	20.41
CO13-SD-U	Underground	3 Gang with blank compartment, Provision for 3 x Square D type QO 2 pole 10 kA rated circuit breaker	3	23½	33½	4¾	45	20.41
CO14	Overhead	4 Gang, Provision for 4 X 2 pole 10 kA rated circuit breaker	4	23½	33½	4¾	60	27.21
CO14-100	Overhead	4 Gang, Comes complete with 4 X 2 pole 100 A 10 kA rated circuit breaker	4	23½	33½	4¾	60	27.21
CO14-100HI	Overhead	4 Gang, Comes complete with 4 X 2 pole 100 A 22 kA rated circuit breaker	4	23½	33½	4¾	60	27.21
CO14-100HI-U	Underground	4 Gang with blank compartment, comes complete with 4 x 2 pole 100 A 22 kA rated circuit breaker	4	23½	41⅞	4¾	60	27.21
CO14-SD	Overhead	4 Gang, Provision for 4 x Square D type QO 2 pole 10 kA rated circuit breaker	4	23½	41⅞	4¾	60	27.21
CO14-SD-U	Underground	4 Gang with blank compartment, Provision for 4 x Square D type QO 2pole 10 kA rated circuit breaker	4	23½	41⅞	4¾	60	27.21


Note: For underground version, add suffix -U.

## CO1 Multi-gang

200 A (main lugs), 100 A per position 120/240 V; multi-gang combination with or without breaker

### Product specifications

- Conductor range: line: 6 AWG–250 kcmil, load: 6–1/0 AWG
- Overhead only – tunnel type connectors for both load and line sides
- Underground only – aluminum tunnel type connector load side (6–1/0 AWG), line side ½ in. studs
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Bottom compartment has provision for 2 pole circuit breaker ( max 100 A ) 10 kA breakers ( 22 kA breaker where indicated HI) Siemens (Q), Eaton (BR), GE (TQL). Only SQD (QO) breakers will fit units with suffix SD.
- Primarily used in: All provinces

 Approved for copper or aluminum

### Diagrams

