

BE1 Series


100 A 600 V; king size

Product specifications

- Conductor range: 6–1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground

- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in all provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



BE1-1 1/4V



Cat. no.	Description	Dimensions (in.)			Weight each	
		H	W	D	lb	kg
4 Jaw						
BE1-V	Overhead, hub opening	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-INV	Overhead, hub opening, comes with insulated neutral	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-1 1/4V	Overhead, hub opening, comes with 1 ¹ / ₄ in. hub	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-1 1/4INV	Overhead, hub opening comes with 1 ¹ / ₄ " hub and insulated neutral	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-1 1/2V	Overhead, hub opening, comes with 1 ¹ / ₂ in. hub	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-TV	Underground	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-INTV	Underground comes with insulated neutral	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-TCV	Combination overhead-underground	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-TCV-CR	Combination overhead-underground, corrosion resistant	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE1-INTCV	Combination overhead-underground comes with insulated neutral	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE11-V-CM	Overhead, twin hub opening	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE11-1 1/4V	Overhead, twin hub opening comes with 1 ¹ / ₄ in. hubs	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
BE11 1/4INV	Overhead, twin hub opening comes with 1 ¹ / ₄ in. hubs and insulated neutral	14 ⁵ / ₁₆	8 ³ / ₄	4 ³ / ₁₆	8	3.6
Factory-installed accessories						
Include: -5		5 th jaw, standard capacity, 9 o'clock position				
-9		5 th jaw, full capacity, 9 o'clock position				
-6		5 th jaw, full capacity, 6 o'clock position				
-IN		Insulated neutral				
-W		Water heater lugs				

Diagrams

