

## BSC4-G Series

400 A (main lugs) 600 V; stud type multiple position with blank compartment  
200 A per position




BSC42-VGA

### Product specifications


- Conductor range: line: single ½ in. studs to accommodate compression lugs (supplied by utility), load: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for load side
- For underground service only
- Twin wiring compartment, increased length of the busbars and double ½ in. studs to accommodate compression lugs
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: Ontario and British Columbia

### For use in Ontario



| Cat. no.               | Meter position | Dimensions (in.)               |                                |                                | Weight each |      |
|------------------------|----------------|--------------------------------|--------------------------------|--------------------------------|-------------|------|
|                        |                | H                              | W                              | D                              | lb          | kg   |
| <b>Left-hand entry</b> |                |                                |                                |                                |             |      |
| BSC42-VG               | 2 position     | 23 <sup>3</sup> / <sub>8</sub> | 35                             | 5 <sup>5</sup> / <sub>16</sub> | 58          | 26.3 |
| BSC43-VG               | 3 position     | 23 <sup>3</sup> / <sub>8</sub> | 43 <sup>3</sup> / <sub>4</sub> | 5 <sup>5</sup> / <sub>16</sub> | 72          | 32.7 |
| BSC44-VG               | 4 position     | 23 <sup>3</sup> / <sub>8</sub> | 52 <sup>1</sup> / <sub>2</sub> | 5 <sup>5</sup> / <sub>16</sub> | 86          | 39.0 |
| BSC45-VG               | 5 position     | 23 <sup>3</sup> / <sub>8</sub> | 61 <sup>1</sup> / <sub>4</sub> | 5 <sup>5</sup> / <sub>16</sub> | 100         | 45.4 |
| BSC46-VG               | 6 position     | 23 <sup>3</sup> / <sub>8</sub> | 70                             | 5 <sup>5</sup> / <sub>16</sub> | 114         | 51.8 |

### For use in British Columbia



| Cat. no.  | Left-hand entry | Right-hand entry | Meter position | Dimensions (in.)               |                                |                                | Weight each |      |
|-----------|-----------------|------------------|----------------|--------------------------------|--------------------------------|--------------------------------|-------------|------|
|           |                 |                  |                | H                              | W                              | D                              | lb          | kg   |
| BSC42-VGA |                 | BSC42-VGAH       | 2 position     | 23 <sup>3</sup> / <sub>8</sub> | 35                             | 5 <sup>5</sup> / <sub>16</sub> | 58          | 26.3 |
| BSC43-VGA |                 | BSC43-VGAH       | 3 position     | 23 <sup>3</sup> / <sub>8</sub> | 43 <sup>3</sup> / <sub>4</sub> | 5 <sup>5</sup> / <sub>16</sub> | 72          | 32.7 |
| BSC44-VGA |                 | BSC44-VGAH       | 4 position     | 23 <sup>3</sup> / <sub>8</sub> | 52 <sup>1</sup> / <sub>2</sub> | 5 <sup>5</sup> / <sub>16</sub> | 86          | 39.0 |
| BSC45-VGA |                 | BSC45-VGAH       | 5 position     | 23 <sup>3</sup> / <sub>8</sub> | 61 <sup>1</sup> / <sub>4</sub> | 5 <sup>5</sup> / <sub>16</sub> | 100         | 45.4 |
| BSC46-VGA |                 | BSC46-VGAH       | 6 position     | 23 <sup>3</sup> / <sub>8</sub> | 70                             | 5 <sup>5</sup> / <sub>16</sub> | 114         | 51.8 |

### Diagrams

