

Nonmetallic liquidtight conduit fittings

Time saving and cost effective.

Nonmetallic liquidtight conduit may be used with nonmetallic, malleable iron or zinc liquidtight fittings, offering a combination of benefits not available from traditional metal liquidtight conduit.

Features

- Chemical resistant
- Corrosion-free
- No metal fatigue or jacket separation
- Crush and abrasive resistant
- Insulated for safety
- Extra rugged and flexible
- Temperature range: -18 °C to 75 °C (0 °F to 167 °F)
- Cold impact resistant
- Lightweight
- Cuts easily
- Prevents hand injuries
- Marked at 1-foot intervals for easy measurement and cutting

Applications

- Electrical motors and controls
- Plating applications
- Water treatment
- Marine equipment
- Heating and refrigeration
- Computer equipment
- Robotics
- Machine tools
- Chemical processing
- Printing equipment
- Fiber optics
- Pumps and related equipment
- Air conditioning
- Etc.

Nonmetallic liquidtight conduit fittings



| | Cat. no. | Trade size (in.) | KO size (in.) | Throat (in.) |
|---|------------|------------------|---------------|--------------|
| Straight | | | | |
| | CILTCC-03 | 5/8 | 1/2 | 0.54 |
| | CILTCC-04 | 1/2 | 1/2 | 0.54 |
| | CILTCC-06 | 3/4 | 3/4 | 0.74 |
| | CILTCC-08 | 1 | 1 | 0.98 |
| CILTCC-03 / CILTCC-08 Supplied with locknut | | | | |
| 90° | | | | |
| | CILTCC-903 | 5/8 | 1/2 | 0.54 |
| | CILTCC-904 | 1/2 | 1/2 | 0.54 |
| | CILTCC-906 | 3/4 | 3/4 | 0.74 |
| | CILTCC-908 | 1 | 1 | 0.98 |
| CILTCC-903 / CILTCC-908 Supplied with locknut | | | | |