EXA SERIES / EXB SERIES D13

# **EXB** series

# 36 AWG individual strand

### **Description:**

2-hole NEMA, extra-flexible braided connectors using 36 AWG individual wires in braid construction for extra flexibility. These connectors are made with tin- or silver-plated high-conductivity 99.9% pure copper ferrules formed on each end. Individual wires used in braid are tinned prior to weaving so that maximum protection from corrosion is provided.

### **Application:**

These highly flexible connectors are suitable wherever it is necessary to take up expansion, severe vibration and/or misalignment when connecting transformers, switchgear, generators or busbars.

## Ordering information:

**Length:** Standard total lengths are 304 mm (12 in.). If different lengths are required, add your desired length in millimeters at the end of the part number. Ex.: EXB040A1**406** (for 16 in. long)

**Plating:** Standard ferrules are electro-tin plated. Other options are available; please refer to page D4.



Extra-flexible connectors - 2-hole NEMA standard

Cat. no.	*Ampacity ∆ 65 °C	No. of braids in assembly	W in. (mm)	F in. (mm)	E in. (mm)	S in. (mm)	H in. (mm)	T in. (mm)	Weight lb (g)
EXB070A1	700	2	1½ (38.1)	3½ (90)	5/8 (16)	1¾ (44.4)	% <sub>16</sub> (14.3)	<del>1</del> / <sub>4</sub> (6.3)	0.97 (440)
EXB090A1	900	3	1½ (38.1)	3½ (90)	5/s (16)	1¾ (44.4)	<sup>9</sup> /16 (14.3)	11/32 (9.5)	1.30 (590)
EXB110A1	1,100	4	1½ (38.1)	3½ (90)	5/s (16)	1¾ (44.4)	%16 (14.3)	3/8 (9.5)	1.66 (753)
EXB150A1	1,500	6	1½ (38.1)	3½ (90)	5/8 (16)	1¾ (44.4)	<sup>9</sup> / <sub>16</sub> (14.3)	½ (12.7)	2.26 (1,025)
EXB170A1	1,700	9	1% (40)	3½ (90)	5/8 (16)	1¾ (44.4)	% <sub>16</sub> (14.3)	3/4 (19)	3.71 (1,683)
EXB200A1	2,000	13	1% (40)	3½ (90)	5⁄8 (16)	13/4 (44.4)	9/16 (14.3)	1 (25.4)	5.21 (2,363)

<sup>\*</sup>Temperature rise test per; CEI60694, IEEE / ANSI C37, 34 1994.

