

Pipe and conduit seals











Flood-Seal® pipe/conduit seals



Rubber-insulated end caps for commercial pipes and conduits.

- Flood-Seal EPDM rubber seals out water, insects, rodents and dirt
- Durable and unaffected by sun, rain or soil
- Ideal for installations or cable replacements
- Tight fitting to prevent accidental removal

Flood-Seal® pipe/conduit seals

Diagrams	Cat. no.	Pipe size		Conductor (AWG or kcmil)	Ranges		Outside body length (in.)
		(IPS)	Style		Decimal		
 Style 1 No Outlets	CIC 75-3	¾	10	#14-#10	-	1½	
	 Style 2 1 Outlet	CIC 50-3	½	10	#14-#10	-	1¾
 Style 3 1 Outlet	CIC 1-4	1	4	(4)#14-#4	SL-0.380	2 ¹³ / ₃₂	
	 Style 4 2, 3, 4 or 6 Outlets	CIC 150	1½	5	-	0.720-1.200	1¾
 Style 5 1 Outlet	CIC 15-320	1½	6	(3)#2-2/0	0.370-0.580	1¾	
	 Style 6 3 or 4 Outlets	CIC 15-420	1½	6	(4)#2-2/0	0.370-0.580	1¾
 Style 7 3 or 4 Outlets	C-5230	2	4	(2)#14-350, (1)#14-1/0	SL-0.910, SL-0.540	1½	
	 Style 8 4 Outlets	C-5035	2	4	(1)#14-350, (1)#14-500	SL-0.980, SL-1.175	1 ¹⁵ / ₁₆
 Style 9 2 or 4 Outlets	C-5231	2	4	(3)#14-350, (1)#14-4/0	SL-0.980, SL-0.690	2	
	 Style 10 3 Outlets	CIC 200	2	5	-	1.093-1.562	2
	CIC 201	2	5	-	0.937-1.145	4	
	PS 2	2	7	(3)#14-250	SL-0.765	1 ³ / ₁₆	
	3133	2½	2	300-1,500	0.760-1.880	2¾	
	3133-6	2½	2	300-1,500	0.760-1.880	6¾	
	CIC 25-440	2½	4	(4)#2-4/0	0.390-0.690	2¼	
	CAP 250	2½	1	-	-	3	
	PS 25	2½	7	(2)#14-350, (1)#14-250	SL-0.980, SL-0.765	1 ³ / ₁₆	
	3135	3	2	350-2,000	0.830-2.234	2½	
	CAP 300	3	1	-	-	2½	
	CVC 3*	3	6	-	(3)1.093-1.562	2 ¹¹ / ₁₆	
	CNC 3-1G	3	9	-	(1)1.031-1.531, (1).280-0.420	2½	
	PS 3	3	7	(3)#14-350, (1)#14-250	SL-0.980, SL-0.765	1 ³ / ₁₆	
	PSX 3	3½	9	(3)#14-350, (1)#14-250	SL-0.980, SL-0.765	2½	
	PSX 35	3½	8	(3)#14-500, (1)#14-250 & 350-500	SL-1.175 SL-0.765	3 ¹⁵ / ₁₆	
	3138	4	4	#14-400	SL-0.980	2	
	6318	4	3	-	1.500-3.00	2 ¹¹ / ₁₆	
	CAP 400	4	1	-	-	2 ¹¹ / ₁₆	
	CNC 4-1G	4	9	-	(1)1.031-1.531, (1).280-0.420	2¾	
	CVC 4*	4	6	-	(3)1.125-1.875	3 ³ / ₁₆	
	PS 4	4	7	(3)#14-500, (1)#14-350	SL-1.175, SL-0.980	1¾	
	CIC 401	4	2	-	0.830-2.234	3¾	
	CAP 500	5	1	-	-	2 ¹⁵ / ₁₆	
	CVC 5*	5	6	-	1.250-2.00	3 ⁷ / ₁₆	
	PS 5	5	7	(3)#2-1500, (1)#14-500	0.370-1.600, SL-1.175	2¾	
	PS 6	6	7	(4)#2-1,500	0.370-1.600	2¾	

* Vent cap, not watertight. Note: For sizes not listed, please consult your ABB representative.