

Copper tees

Tin-plated tees



250 T 250

Tees available in many run and tap sizes for various copper conductors

- High conductivity, resistant to corrosion
- Easy identification

Tin-plated tees

Cat. no.	Conductor size (AWG or kcmil)	
	Run	Tap
2 T 2	#2	#2
1/0 T 6	1/0	#6
1/0 T 4	1/0	#4
1/0 T 2	1/0	#2
1/0 T 1	1/0	#1
1/0 T 1/0	1/0	1/0
2/0 T 6	2/0	#6
2/0 T 4	2/0	#4
2/0 T 2	2/0	#2
2/0 T 1	2/0	#1
2/0 T 1/0	2/0	1/0
2/0 T 2/0	2/0	2/0
3/0 T 1/0	3/0	1/0
3/0 T 3/0	3/0	3/0
4/0 T 2	4/0	#2
4/0 T 1	4/0	#1
4/0 T 1/0	4/0	1/0
4/0 T 2/0	4/0	2/0
4/0 T 4/0	4/0	4/0
250 T 2	250	#2
250 T 1	250	#1
250 T 1/0	250	1/0
250 T 2/0	250	2/0
250 T 4/0	250	4/0
250 T 250	250	250
300 T 300	300	300

Cat. no.	Conductor size (AWG or kcmil)	
	Run	Tap
350 T 1/0	350	1/0
350 T 2/0	350	2/0
350 T 4/0	350	4/0
350 T 350	350	350
400 T 1/0	400	1/0
400 T 2/0	400	2/0
400 T 4/0	400	4/0
400 T 250	400	250
400 T 300	400	300
400 T 350	400	350
400 T 400	400	400
500 T 1/0	500	1/0
500 T 2/0	500	2/0
500 T 4/0	500	4/0
500 T 250	500	250
500 T 350	500	350
500 T 400	500	400
500 T 500	500	500
600 T 2/0	600	2/0
600 T 4/0	600	4/0
600 T 350	600	350
600 T 500	600	500
600 T 600	600	600
750 T 350	750	350
750 T 500	750	500
750 T 750	750	750
1000 T 500	1,000	500
1000 T 1000	1,000	1,000

Copper tees

Tin-plated tapered tees



TT 350-350


Tapered ends enable use in high-voltage applications up to 69 kV

- Provides high conductivity
- Resists corrosion

Tin-plated tapered tees

Cat. no.	Run	Tap	Dimensions (in.)	
			L	T
TT 2-2	#2	#2	3 ¹¹ / ₁₆	1½
TT 1/0-6	1/0	#6	3 ³ / ₁₆	1½
TT 1/0-4	1/0	#4	3 ¹³ / ₁₆	1½
TT 1/0-2	1/0	#2	3 ⁷ / ₈	1½
TT 1/0-1	1/0	#1	3 ¹⁵ / ₁₆	1½
TT 1/0-1/0	1/0	1/0	4	1½
TT 2/0-6	2/0	#6	3 ²⁹ / ₃₂	1½
TT 2/0-4	2/0	#4	3 ³¹ / ₃₂	1½
TT 2/0-2	2/0	#2	4 ¹ / ₃₂	1½
TT 2/0-1	2/0	#1	4 ³ / ₃₂	1½
TT 2/0-1/0	2/0	1/0	4 ⁵ / ₃₂	1½
TT 2/0-2/0	2/0	2/0	4 ⁵ / ₃₂	1½
TT 3/0-1/0	3/0	1/0	4 ⁷ / ₁₆	1 ⁵ / ₈
TT 3/0-3/0	3/0	3/0	4 ⁷ / ₁₆	1 ⁵ / ₈
TT 4/0-2	4/0	#2	4 ³ / ₁₆	1 ³ / ₄
TT 4/0-1	4/0	#1	4 ³ / ₁₆	1 ³ / ₄
TT 4/0-1/0	4/0	1/0	4 ¹ / ₄	1 ³ / ₄
TT 4/0-2/0	4/0	2/0	4 ⁵ / ₁₆	1 ³ / ₄
TT 4/0-4/0	4/0	4/0	4 ⁷ / ₁₆	1 ³ / ₄
TT 250-2	250	#2	4 ¹ / ₄	1 ³ / ₄
TT 250-1	250	#1	4 ¹ / ₄	1 ³ / ₄
TT 250-1/0	250	1/0	4 ⁵ / ₁₆	1 ³ / ₄
TT 250-2/0	250	2/0	4 ³ / ₈	1 ³ / ₄
TT 250-4/0	250	4/0	4 ¹ / ₂	1 ³ / ₄
TT 250-250	250	250	4 ³ / ₁₆	1 ³ / ₄
TT 300-300	300	300	4 ³ / ₁₆	1 ³ / ₄

Cat. no.	Run	Tap	Dimensions (in.)	
			L	T
TT 350-1/0	350	1/0	5 ³⁷ / ₆₄	2 ¹³ / ₁₆
TT 350-2/0	350	2/0	5 ³⁷ / ₆₄	2 ¹³ / ₁₆
TT 350-4/0	350	4/0	5 ²³ / ₃₂	2 ¹³ / ₁₆
TT 350-350	350	350	5 ²⁹ / ₃₂	2 ¹³ / ₁₆
TT 400-1/0	400	1/0	5 ²¹ / ₃₂	2 ³ / ₈
TT 400-2/0	400	2/0	5 ²¹ / ₃₂	2 ³ / ₈
TT 400-4/0	400	4/0	5 ²⁵ / ₃₂	2 ³ / ₈
TT 400-250	400	250	5 ²⁷ / ₃₂	2 ³ / ₈
TT 400-300	400	300	5 ²⁹ / ₃₂	2 ³ / ₈
TT 400-400	400	400	6 ¹ / ₃₂	2 ³ / ₈
TT 500-1/0	500	1/0	6 ²³ / ₆₄	2 ¹⁹ / ₃₂
TT 500-2/0	500	2/0	6 ²³ / ₆₄	2 ¹⁹ / ₃₂
TT 500-4/0	500	4/0	6 ¹⁵ / ₃₂	2 ¹⁹ / ₃₂
TT 500-250	500	250	6 ¹⁷ / ₃₂	2 ¹⁹ / ₃₂
TT 500-350	500	350	6 ²¹ / ₃₂	2 ¹⁹ / ₃₂
TT 500-400	500	400	6 ²³ / ₃₂	2 ¹⁹ / ₃₂
TT 500-500	500	500	6 ²³ / ₃₂	2 ¹⁹ / ₃₂
TT 600-2/0	600	2/0	7 ³ / ₁₆	3 ³ / ₃₂
TT 600-4/0	600	4/0	7 ¹ / ₁₆	3 ³ / ₃₂
TT 600-350	600	350	7 ⁹ / ₁₆	3 ³ / ₃₂
TT 600-500	600	500	7 ¹¹ / ₁₆	3 ³ / ₃₂
TT 600-600	600	600	7 ⁷ / ₈	3 ³ / ₃₂
TT 750-350	750	350	9 ¹ / ₂	4 ¹ / ₄
TT 750-500	750	500	9 ¹ / ₂	4 ¹ / ₄
TT 750-750	750	750	9 ¹ / ₂	4 ¹ / ₄
TT 1000-500	1,000	500	9 ¹ / ₂	4 ¹ / ₄
TT 1000-1000	1,000	1,000	9 ¹ / ₂	4 ¹ / ₄



Copper tees



2131-20

- Provides high strength and high conductivity
- Resists corrosion

Cat. no.	Conductor size (AWG or kcmil)		Dimensions (in.)		
	Run	Tap	B	L	W
2131-1	750	2/0 str.	1½	4⅞	2½ ₁₆
2131-2	750	4/0 str.	1⅝	5	2½ ₁₆
2131-3	750	250	1⅝	5	2½ ₁₆
2131-4	750	350	2	5⅝	2½ ₁₆
2131-5	750	500	2¼	5⅝	2½ ₁₆
2131-6	750	750	2⅞	6¼	2½ ₁₆
2131-7	1,000	2/0 str.	1½	4⅞	2½ ₁₆
2131-8	1,000	4/0 str.	1⅝	5	2½ ₁₆
2131-9	1,000	250	1⅝	5	2½ ₁₆
2131-10	1,000	350	2	5⅝	2½ ₁₆
2131-11	1,000	500	2¼	5⅝	2½ ₁₆
2131-12	1,000	750	2⅞	6¼	2½ ₁₆
2131-13	1,000	1,000	3	6⅝	2½ ₁₆
2131-14	1,500	2/0 str.	1½	4⅞	2½ ₁₆
2131-15	1,500	4/0 str.	1⅝	5	2½ ₁₆
2131-16	1,500	250	1⅝	5	2½ ₁₆
2131-17	1,500	350	2	5⅝	2½ ₁₆
2131-18	1,500	500	2¼	5⅝	2½ ₁₆
2131-19	1,500	750	2⅞	6¼	2½ ₁₆
2131-20	1,500	1,000	3	6⅝	2½ ₁₆
2131-21	1,500	1,500	3¾ ₁₆	6⅞	2½ ₁₆
2131-22	1,500	2,000	3¾	8	2½

Diagram

