**new** product



# **EXP LED "Exit" Series**

Battery Units, Self-Powered Exit Signs Combination Units

#### CSA certified for use in hazardous locations.

The EXP LED EXIT Series of battery equipment is designed to cover emergency lighting applications for the entire spectrum of hazardous locations, where inflammable gases, vapors, liquids, dust particles, fabrics or tissues are permanently present or are likely to exist.

The EXP LED EXIT Series combines in one simple-to-order catalogue family three traditional emergency lighting products with battery back-up: battery units with emergency lights, Self-Powered Exit Signs, and combination units with emergency lights and Exit Sign. The equipment is also available with additional emergency power capacity to drive remote heads and Exit Signs.

#### **FEATURES**

- CSA Certified for use in hazardous locations:
  - Class I, Division 1, Groups B, C, D
  - Class I, Division 2, Groups A, B, C, D
  - Class II. Divisions 1 and 2. Groups E. F. G
  - Class III. Divisions 1 and 2
- For wall mount only
- Die-Cast aluminum body with grey epoxy powder coat finish; clear, impact and heat resistant prismatic glass globe
- Long-life, maintenance-free Lead-Calcium battery
- Battery charger is current limited, temperature compensated, short-circuit proof and reverse polarity protected
- Emergency heads with one or twin lamp design
- Large Self-Powered exit (combo) includes a transfer circuit to drive three (3) remote LED-based remote Exit Signs (total power max 15W)
- Self-Powered combo includes a transfer panel to drive three remote LED based remote Exit Signs
- Meets or exceeds CSA C22.2 No. 141-10 & No. 137 See warranty details at: http://www.tnb.ca/en/brands/emergi-lite/





#### TYPICAL SPECIFICATIONS

Supply and install the Emergi-Lite® EXP EXIT LED Series of hazardous location battery unit equipment. The battery unit housing will be constructed of die cast aluminum with grey epoxy powder coat finish and equipped with heavy-duty key holes for wall mount. The equipment shall be rated for 120, 277 or 347V, 60 Hz input and be CSA listed. The equipment shall have an output of \_\_\_\_  $\_$  V and  $\_$ and shall supply the rated load for a minimum of a 1/2 hour to 87,5% of the rated battery voltage. The battery shall be a long-life, maintenancefree lead-calcium type. The charger shall be fully computer tested and have its charge voltage set in the factory to  $\pm$  1% tolerance. The charger shall be current limited, temperature compensated, short circuit proof and reverse polarity protected. The charger shall be furnished with an electronic lockout circuit, which will connect the battery when the AC circuit is activated, and an electronic brownout circuit.

Where required the equipment shall come complete with heads, each of them equipped with \_  $_{\rm lamp(s)}$  of  $_{\rm l}$ 

The head housing shall be Die-Cast aluminum with grey epoxy powder coat finish. The lenses shall be a clear, impact and heat resistant prismatic glass globe. The head shall be factory sealed, with no need for external seals.

Where required the equipment shall come complete with one Pictogram Exit Sign and will include a transfer circuit to maintain the Pictogram Sign permanently lighting in both normal and emergency operation. The picto housing shall be industrial grade 14-gauge steel and finished in grey enamel. The faceplate will be constructed of heavy-duty 14-gauge steel.


The equipment shall be certified CSA C22.2 No.137-M1981 for Hazardous Locations: Class \_\_\_\_\_, Division \_\_\_\_\_, Group \_\_\_\_\_ with the temperature code

The Exit Sign shall be CSA C22.2 No.141-10 certified.

The equipment shall be Emergi-Lite® Model: \_

#### **DIMENSIONS**

Dimensions are approximate and subject to change



**new** product

# **EXP LED "Exit" Series**

Battery Units, Self-Powered Exit Signs Combination Units



#### POWER CONSUMPTION AND UNIT RATING

UNIT CAPACITY	AC SPECS			WATTAGE CAPACITY				
UNIT CAPACITY	INPUT VOLTAGE	INPUT RATING	30MIN	1H	1H30	2H	4H	
12V-72W <sup>1</sup>	120V, 60Hz	0.25A, 25W		36	25	20	10	
	277V, 60Hz	0.125A, 28W	72					
	347V, 60 Hz	0.115A, 28W						
12V-120W	120V, 60Hz	0.45A, 37W		60	40	30	15	
	277V, 60Hz	0.209A, 42W	120					
	347V, 60 Hz	0.176A, 42W						
24V-144W	120V, 60Hz	0.465A, 38W		72	50	40	20	
	277V, 60Hz	0.208A, 42W	144					
	347V, 60 Hz	0.178A, 42W						

<sup>&</sup>lt;sup>1</sup> Combo, no remote Exit capability.

### TEMPERATURE CODES: MEASURED AT 40°C AMBIENT

Explosion-proof equipment is composed of one or more modules, each of them qualified for a specific temperature code. The temperature code of the complete equipment (enclosure + exit sign + emergency heads) is defined as the most severe of the temperature codes identified for each of the modules below.

## TEMPERATURE CODES FOR EXP-P SERIES (Battery & sign combination units)

SEVERITY CODE	S1	S2	S3	S4
TEMPERATURE CODE	T6 85°C (185°F)	T6 85°C (185°F)	T6 120°C (248°F)	T6 85°C (185°F)

### **EXP SEVERITY CODE SELECTION CHART**

ENVIRONMENT	SEVERITY CODE
Cl. I, Div. 1 & 2, Gr. B	S1
Cl. I, Div. 1, Gr. C, D	S2
Cl. I, Div. 2, Gr. A, B, C, D	S3
Cl. II, Div. 1 & 2, Gr. E, F, G & Cl. III	S4

#### **EXP**

SERIES	CAPACITY	A.C VOLTAGE	OPTIONS	SIGN/FACE	HEAD STYLE	SEVERITY CODE	LAMP TYPE, VOLTAGE & POWER
<b>12EXP</b> = 12V	<b>72</b> = 72W <sup>1</sup> <b>120</b> = 120W	<b>Blank</b> = 120VAC -2= 277VAC input -3= 347VAC input	Blank= No options D= Time delay	Blank= No sign E1= Single face LED "EXIT"	Blank= No heads /11= Single remote, 1 lamp	<b>\$1</b> = Cl.I, Div.1&2, Gr.B <b>\$2</b> = Cl.I, Div.1, Gr. C, D <b>\$3</b> = Cl.I, Div.2, Gr. A, B,	<b>Blank</b> = No lamp <b>LG</b> = 12V-4W MR16 LED <b>LI</b> = 12V-5W MR16 LED
<b>24EXP</b> = 24V	<b>144</b> = 144W		(15 min.) <b>TS=</b> Transfer switch <sup>1</sup>	E2= Double face LED "EXIT"	/12= Single remote, 2 lamps /21= Double remote, 1 lamp each <sup>1</sup>	C, D <b>S4=</b> Cl.II, Div.1&2, Gr. E, F, G & CLIII	LJ= 12V-6W MR16 LED LL= 24V-4W MR16 LED
	<sup>1</sup> Combo, no remote Exit capability		<sup>1</sup> Not available with 12V-72W		<sup>1</sup> Not available with exit sign		

EXAMPLE: 12EXP72-2E1/11S1LG