Ε

Kopex-Ex[™] - Hazardous location conduit and fittings



Ε

Kopex-Ex - Hazardous location conduit and fittings

Table of contents

Section E

Hazardous areas	E4
Product marking guide	E8
Liquidtight flexible metallic conduit system	E10
Liquidtight hazardous areas fittings	E14
XP Flex™ couplers	E18
Enlargers, reducers and thread convertors	E20
Stopping plugs	E26
Couplers, sealing washers and locknuts	E28
Ev standards worldwide	E30

Hazardous areas

Applications

Protection for critical wiring in hazardous areas

From our UK-based facility, ABB manufactures a wide range of globally approved products, including metallic conduit and fittings along with a full range of conduit accessories.

We are committed to an extensive and ongoing product development program, which will continue to deliver innovative and high performance products for effective cable protection in safetycritical areas.

Our current range of high performance products is designed for many highly demanding market sectors, including petrochemical, pharmaceutical and offshore industries or any ATEX/IECEx/UL/CSA areas.

ATEX/IECEx

The directive is designed to harmonize the law of EU member states concerning equipment and protective systems intended for use in potentially explosive areas.

Products are categorized 1, 2 and 3 with category 1 meaning the product employs a very high level of protection; category 2, a high level of protection; category 3, a normal level of protection.

Its main requirements are the need to classify areas as Zones 0, 1 and 2 (for gases and vapours) and Zones 20, 21, 22 (for dusts and equipment for mining). Mining applications are covered by Group I and non-mining applications by Group II.





UL/CSA directives

Products are categorized into Classes and Divisions (UL) or Zones (CSA), where Class I denotes use in gas environments and Class II, dust and flyings.

This Class and Division or Zone system identifies what equipment can be used as stated in the NEC National Electrical Code or CEC Canadian Electrical Code, Part I.





Technical support

ABB can provide technical assistance in the selection of the appropriate product from its range. For help, please contact your regional sales office.



HAZARDOUS AREAS E5

Hazardous areas

Standards and what they mean

Zone definitions - Dust (as per ATEX 60079)

20NE

Zone 20

Permanent/frequent

Area in which an explosive atmosphere in the form of a cloud of combustible dust in air is **present continuously**, or for long periods, or frequently.



Occasional


Area in which an explosive atmosphere, in the form of a cloud of combustible dust in air is **likely to occur**, in normal operation, occasionally.



Zone 22 _ _ _ _ _ _ Dust irregular/short duration

Area in which an explosive atmosphere, in the form of a cloud of combustible dust in air is **not likely to occur** in normal operation but, if it does occur, will persist for a **short period** only.





Hazardous areas

Standards and what they mean


Zone definitions – Gases and vapours (as per ATEX 60079-10)

Zone 0 Permanent/frequent Place in which an explosive atmosphere consisting of a mixture of air and flammable substances in the form of gas, vapour or mist is present continuously or for long periods, or frequently.	ZONE 1 Zone 1 Occasional Place where an atmosphere consisting of a mixture of air and flammable substances in the form of gas, vapour or mist is likely to arise occasionally during normal operation.	

HAZARDOUS AREAS E7


Hazardous areas

Standards and what they mean



Product marking guide

Classification of equipment for use in potentially explosive atmospheres




PRODUCT MARKING GUIDE

Product marking guide

Classification of equipment for use in potentially explosive atmospheres

Application	Type of protection		Marking	EN/IEC standard
All applications	General requirements		-	60079-0
Control stations, motors, fuses, switchgear, power electronics	Flameproof enclosure	多。	Exd	60079-1
Installation materials, motors, luminaries	Increased safety	X	Exe	60079-7
Measurement and control, automation technology, sensors, actuators	Intrinsic safety		Exi	60079-11
Switch- and control cupboards, analyse- apparatus, computers	Pressurisation	多。	Ехр	60079-2
Coils of motors or relays, solenoid valves	Encapsulation	包	Exm	60079-18
Transformers, relays, control stations, magnetic contactors	Oil immersion	包	Exo	60079-6
Capacitors, transformers	Powder filling	[]	Exq	60079-5
See at the top - only for zone 2	'Non sparking'		Exn	60079-15
For use in zone 0, 1, 2 / for use in zone 1, 2	Dust atmospheres		Ext	60079-31



IIA T1 Ammonia 630° IIA T1 Bensene 560°

IIB T1 Carbon monoxide 605°

IIC T1 Hydrogen 560°

IIA T1 Acetone 735°

IIA T1 Methane 537°

IIA T1 Toluene 535°

IIA T1 Styrene 490°

IIA T1 Propane 470°

IIA T1 1-Butene 455°

IIB T1 Butadiene 430°

IIB T2 Ethylene 425°

IIA T2 Butane 372°

IIA T2 Ethanol 363°

IIA T2 Butylalcohol 359°

IIB T2 Dimetylether 350°

IIC T2 Acetylene 305°

IIA T3 Nafta 290°

IIA T3 Hydrogen sulphide 270°

IIA T3 Cyclohexane 259°

IIA T3 Hexane 233°


IIA T3 Heptane 215°

IIA T3 Kerosene 210°

IIA T3 Dekane 201°

IIB T4 Diethyl ether 160°

IIC T6 Carbon disulphide 95°



New marking — EPLs (explosion protection levels)

The introduction of the EPLs and changes in the EN 60079 series standard has introduced new marking requirements.

_

Liquidtight flexible metallic conduit system

Certification and characteristics – Steel cores

General oil resistant — Galvanized steel core with a general purpose oil-resistant coating



Certification standard: IEC 61386 Static Temp: -25 °C to +105 °C Flexing Temp: -5 °C to +105 °C Special characteristics:
Flame-retardant PVC covering
Flame propogation:

Flame dies in less than 30 seconds after ignition source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLB0510

_

Low fire hazard - Galzanized steel core with an LFH coating



Certification standard: IEC 61386 LUL fully compliant (E1042A6) MOD to NES 518: Issue 3 DEF STAN 61-12 (Part 31)

Static temp: -25 °C to +90 °C Flexing temp: -5 °C to +90 °C Special characteristics:

Limited fire hazard, zero halogen (BS6425 Pt 1)

Flame propogation:

Flame dies in less than 30 seconds after ignition source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLT0510

_

High temperature - Galvanized steel core with a high temperature-resistant coating



Certification standard: IEC 61386 Static temp: -50 °C to +130 °C Flexing temp: -5 °C to +90 °C Special characteristics: Flame resistance: UL94 V2 Chemical and oil resistant Flame propogation:

Flame dies in less than 30 seconds after ignition source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLH0510

_

Low fire hazard with EMC protection – Galvanized steel core with a galvanized steel EMC shield and LFH covering



Certification standard:

IEC 61386

MOD to NES 518: Issue 3 DEF STAN 61-12 (Part 31)

Issue 1

Static temp: -25 °C to +90 °C Flexing temp: -5 °C to +90 °C

Special characteristics:

Limited fire hazard covering

EMC Screening level: 60 db at 1 MHz braided

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

*Add coil length to complete part number, e.g. 10 metres = EXBBT0510

—

High temperature highly flexible - Galvanized steel core with a high temperature, highly flexible coating



Certification standard: IEC 61386 Static temp: -65 °C to +150 °C Flexing temp: -45 °C to +135 °C **Special characteristics:** High flexibility

High temperature Flame propagation:

Flame dies in less than 30 seconds after ignition source is removed

Related products



Group I and II gland pages E14–E15



Universal gland pages E16-E17



90° Elbow gland pages E14–E15



Group II gland pages E14–E15

Liquidtight flexible metallic conduit system

Technical specifications – Steel cores

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	1½	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Туре	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
General oil-resistant	(black)	EXLB03*	EXLB04*	EXLB05*	EXLB06*	EXLB07*	EXLB08*	EXLB09*

1	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Туре	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
Low fire hazard (black)		EXLT03*	EXLT04*	EXLT05*	EXLT06*	EXLT07*	EXLT08*	EXLT09*

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	• • •				32	-		03
	US trade size (in.)	3∕6	1/2	3/4	1	1¼	1½	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Туре	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
High temperature	e (black)	EXLH03*	EXLH04*	EXLH05*	EXLH06*	EXLH07*	-	-
High temperature	e (blue)	EXLB03*	EXLB04*	EXLB05*	EXLB06*	EXLB07*	-	-

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Туре	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
Low fire hazard with EMC (black)		EXBBT03*	EXBBT04*	EXBBT05*	EXBBT06*	EXBBT07*	EXBBT08*	EXBBT09*

See note 1 Type	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
High temperature highly flexible (black)		EXLHC03*	EXLHC04*	EXLHC05*	EXLHC06*	EXLHC07*	EXLHC08*	EXLHC09*

*Add coil length to complete part number, e.g. 10 metres = EXLHC0510 $\,$

Liquidtight flexible metallic conduit system

Certification and characteristics – Stainless steel 316 cores

General oil resistant - Stainless steel 316 core with a general purpose oil-resistant coating



Certification standard:

IEC 61386

Static temp: -25 $^{\circ}$ C to +105 $^{\circ}$ C Flexing temp: -5 $^{\circ}$ C to +105 $^{\circ}$ C

Special characteristics:

Flame-retardant PVC covering

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLB0510

_

Low fire hazard - Stainless steel 316 core with an LFH coating



Certification standard:

IEC 61386

LUL fully compliant (E1042A6)

MOD to NES 518: Issue 3 DEF STAN 61-12 (Part 31)

Issue 1

Static temp: -25 °C to +90 °C Flexing temp: -5 °C to +90 °C Special characteristics:

Limited fire hazard, zero halogen (BS6425 Pt 1)

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLT0510

_

High temperature - Stainless steel 316 core with a high temperature-resistant coating



Certification standard:

IEC 61386

Static temp: -50 °C to +130 °C Flexing temp: -5 °C to +130 °C

Special characteristics:

Flame resistance: UL94 V2 Chemical and oil resistant

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLH0510

Low fire hazard with EMC protection – Stainless steel 316 core with a galvanized steel EMC shield and LFH covering



Certification standard:

IEC 61386, UL full compliant

MOD to NES 518: Issue 3 DEF STAN 61-12 (Part 31)

Issue 1

Static temp: -25 °C to +90 °C

Flexing temp: -5 °C to +90 °C

Special characteristics:

Zero halogen (BS6425 pt1) limited fire hazard covering EMC screening level: 60 db at 1 MHz

braided

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

*Add coil length to complete part number, e.g. 10 metres = EXLBBT0510

_

High temperature highly flexible – Stainless steel 316 core with a high temperature, highly flexible coating



Certification standard:

IEC 61386

Static temp: -65 °C to +150 °C Flexing temp: -45 °C to +135 °C

Special characteristics:

High flexibility High temperature

Flame propogation:

Flame dies in less than 30 seconds after ignition

source is removed

Related products



Group I and II gland pages E14–E15



Universal gland pages E16–E17



90° Elbow gland pages E14–E15



pages E14-E15

Liquidtight flexible metallic conduit system

Technical specifications – Stainless steel 316 cores

	Nominal conduit size (mm)	16	20	25	32	40	50	63
See note 1 Type	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
General oil-resis	General oil-resistant (black)		EXSB04*	EXSB05*	EXSB06*	EXSB07*	EXSB08*	EXSB09*

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3∕8	1/2	3/4	1	11/4	11/2	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Type	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
Low fire hazard (b	lack)	EXST03*	EXST04*	EXST05*	EXST06*	EXST07*	EXST08*	EXST09*

	Nominal conduit size (mm)	16	20	25	32	40	50	63
See note 1 Type	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
High temperatu	re (black)	EXSH03*	EXSH04*	EXSH05*	EXSH06*	EXSH07*	_	_
High temperatur	re (blue)	EXSLLH03*	EXSLLH04*	EXSLLH05*	EXSLLH06*	EXSLLH07*	_	_

1	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Type	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
Low fire hazard with EMC (black)		EXSBBT03*	EXSBBT04*	EXSBBT05*	EXSBBT06*	EXSBBT07*	EXSBBT08*	EXSBBT09*

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	US trade size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
See note 1	Inside diameter (mm)	12.5	16.0	21.0	26.4	35.3	40.4	51.6
Туре	Coil lengths (m)	10/30	10/30	10/30	10/20	10/20	10/20	10/20
High temperatu	re highly flexible (black)	EXSHC03*	EXSHC04*	EXSHC05*	EXSHC06*	EXSHC07*	EXSHC08*	EXSHC09*

^{*}Add coil length to complete part number, e.g. 10 metres = EXLHC0510

Liquidtight hazardous areas glands


Certification and characteristics



Flameproof gland

Constructed from either brass or stainless steel, with an epoxy resin barrier, the Group I flameproof gland is a high quality, high specification product, ideal for Ex I and II 2 GD gas and dust, Exde IIC and Exe II applications, Extb II applications, as well as CSA Class 1 Div 2 hazardous locations.

ATEX flameproof G1 gland - Group I and II, Zones 1, 2, 21 and 22, Class I Div2 ABCD, Class II Div1 EFG



Certification standard: Sira 09 ATEX 1231X, IECEx Sira 09.0103X Exde I Mb Exde IIC Gb Extb IIIC Db CSA certified Class I Div 2 ABCD

Temperature: -60 °C to +130 °C

Class II Div 1 EFG

ATEX flameproof 90° elbow gland – Group I and II, Zones 1, 2, 21 and 22, Class I Div1 BCD (rigid conduit only) Class II Div1 EFG





zone 2

DIV 1

(Extb)





Certification standard: Sira 09 ATEX 1231X, IECEx Sira 09.0103X Exde I Mb Exde IIC Gb Extb IIIC Db CSA certified Class I Div 1 BCD (rigid conduit only) Class I Div 2 ABCD Class II Div 1 EFG

Temperature: -60 °C to +130 °C

ATEX flameproof Group II gland – Group II, Zones 1, 2, 21 and 22















Certification standard: Baseefa 06 ATEX 0256X IECEx Bas 06.0059X Exd IIC

Exe II ExtD A21

Temperature: -60 °C to +80 °C

Related products









General oil resistant pages E10-E13

High temperature conduit pages E10-E13

Low fire flexible conduit pages E10-E13

_

Liquidtight hazardous areas glands

Technical specifications

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	Metric thread size (mm)	20	20	25	32	40	50	63
Туре	NPT thread size (in.)	1/2	1/2	3/4	1	11/4	11/2	2
Metric -	Brass	HAM0304G1	HAM0404G1	HAM0505G1	HAM0606G1	HAM0707G1	HAM0808G1	HAM0909G1
Metric -	- Nickel plated	HAMM0304G1	HAMM0404G1	HAMM0505G1	HAMM0606G1	HAMM0707G1	HAMM0808G1	HAMM0909G1
Metric -	- Stainless steel	HAMS0304G1	HAMS0404G1	HAMS0505G1	HAMS0606G1	HAMS0707G1	HAMS0808G1	HAMS0909G1
NPT thr	ead – Brass	HAA0304G1	HAA0404G1	HAA0505G1	HAA0606G1	HAA0707G1	HAA0808G1	HAA0909G1
NPT thr	ead – Nickel plated	HAAM0304G1	HAAM0404G1	HAAM0505G1	HAAM0606G1	HAAM0707G1	HAAM0808G1	HAAM0909G1
NPT thr	ead – Stainless steel	HAAS0304G1	HAAS0404G1	HAAS0505G1	HAAS0606G1	HAAS0707G1	HAAS0808G1	HAAS0909G1

See pages E10–E13 for suitable conduit

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	Metric thread size (mm)	20	20	25	32	40	50	63
Туре	NPT thread size (in.)	1/2	1/2	3/4	1	11/4	11/2	2
Metric – B	Brass	HAM0304E	HAM0404E	HAM0505E	HAM0606E	HAM0707E	HAM0808E	HAM0909E
Metric - N	lickel plated	HAMM0304E	HAMM0404E	HAMM0505E	HAMM0606E	HAMM0707E	HAMM0808E	HAMM0909E
NPT threa	ad – Brass	HAA0304E	HAA0404E	HAA0505E	HAA0606E	HAA0707E	HAA0808E	HAA0909E
NPT threa	ad – Nickel plated	HAAM0304E	HAAM0404E	HAAM0505E	HAAM0606E	HAAM0707E	HAAM0808E	HAAM0909E

 $See pages \ E10-E13 \ for suitable \ conduit. \ *Stainless \ steel \ available \ but \ elbow \ is \ nickel-plated \ brass. \ **Elbow \ supplied \ is \ for \ Liquid \ tight \ conduit \ only \ is \ for \ brass. \ **Elbow \ supplied \ is \ for \ Liquid \ tight \ conduit \ only \ is \ for \ brass. \ **Elbow \ supplied \ is \ for \ brass. \ for \ brass. \ for \ brass. \ for \ for \ brass. \ for \ fo$

	Nominal conduit size (mm)	16	20	25	32	40	50	63
	Metric thread size (mm)	20	20	25	32	40	50	63
Туре	NPT thread size (in.)	1/2	1/2	3/4	1	11/4	11/2	2
Metric – I	Brass	HAM0304	HAM0404	HAM0505	HAM0606	HAM0707	HAM0808	HAM0909
Metric – I	Nickel plated	HAMM0304	HAMM0404	HAMM0505	HAMM0606	HAMM0707	HAMM0808	HAMM0909
Metric -	Stainless steel	HAMS0304	HAMS0404	HAMS0505	HAMS0606	HAMS0707	HAMS0808	HAMS0909
NPT thre	ead – Brass	HAA0304	HAA0404	HAA0505	HAA0606	HAA0707	HAA0808	HAA0909
NPT thre	ead – Nickel plated	HAAM0304	HAAM0404	HAAM0505	HAAM0606	HAAM0707	HAAM0808	HAAM0909
NPT thre	ead – Stainless steel	HAAS0304	HAAS0404	HAAS0505	HAAS0606	HAAS0707	HAAS0808	HAAS0909

See pages E10–E13 for suitable conduit

Liquidtight hazardous areas glands

Certification and characteristics



Flameproof gland

Constructed from either brass or stainless steel, with an epoxy resin barrier, the Group I universal flameproof gland is a high quality, high specification product, ideal for Ex I and II 2 GD gas and dust, Exde IIC, Exe II applications and Extb II applications.

Universal gland – Group I and II, Zones 1, 2, 21 and 22, Class I Div1 BCD (rigid conduit only), Class II Div1 EFG







(Extb)

















Sira 09 ATEX 1231X, IECEx Sira 09.0103X Exde I Mb Exde IIC Gb Extb IIIC Db CSA certified Class I Div 1 BCD (rigid conduit only) Class I Div 2 ABCD

Class II Div 1 EFG Temperature: -60 °C to +130 °C

Universal swivel gland - Group I and II, Zones 1, 2, 21 and 22, Class I Div1 BCD (rigid conduit only) Class II Div1 EFG





ZONE 1



ZONE 2


















Sira 09 ATEX 1231X, IECEx Sira 09.0103X Exde I Mb Exde IIC Gb Extb IIIC Db CSA certified Class I Div 1 BCD (rigid conduit only) Class I Div 2 ABCD Class II Div 1 EFG

Temperature: -60 °C to +130 °C





Liquidtight hazardous areas glands

Technical specifications


Metric	thread size (mm)	20	20	25	32	40	50	63
Туре	NPT thread size (in.)	3/8	1/2	3/4	1	11/4	1½	2
Metric – Bra	ass	HAM0304U	HAM0404U	HAM0505U	HAM0606U	HAM0707U	HAM0808U	HAM0909U
Metric - Nic	ckel plated	HAMM0304U	HAMM0404U	HAMM0505U	HAMM0606U	HAMM0707U	HAMM0808U	HAMM0909U
Metric – Sta	ainless steel	HAMS0304U	HAMS0404U	HAMS0505U	HAMS0606U	HAMS0707U	HAMS0808U	HAMS0909U
NPT thread	d – Brass	HAA0304U	HAA0404U	HAA0505U	HAA0606U	HAA0707U	HAA0808U	HAA0909U
NPT thread	d – Nickel plated	HAAM0304U	HAAM0404U	HAAM0505U	HAAM0606U	HAAM0707U	HAAM0808U	HAAM0909U
NPT thread	d – Stainless steel	HAAS0304U	HAAS0404U	HAAS0505U	HAAS0606U	HAAS0707U	HAAS0808U	HAAS0909U

For use with all threaded conduit including rigid

Metric thread size (mm)	20	20	25	32	40	50	63
Type NPT thread size (in.)	3/8	1/2	3/4	1	11/4	11/2	2
Metric - Brass	HAM0304U/SW	HAM0404U/SW	HAM0505U/SW	HAM0606U/SW	HAM0707U/SW	HAM0808U/SW	HAM0909U/SW
Metric - Nickel plated	HAMM0304U/SW	HAMM0404U/SW	HAMM0505U/SW	HAMM0606U/SW	HAMM0707U/SW	HAMM0808U/SW	HAMM0909U/SW
Metric - Stainless steel	HAMS0304U/SW	HAMS0404U/SW	HAMS0505U/SW	HAMS0606U/SW	HAMS0707U/SW	HAMS0808U/SW	HAMS0909U/SW
NPT thread - Brass	HAA0304U/SW	HAA0404U/SW	HAA0505U/SW	HAA0606U/SW	HAA0707U/SW	HAA0808U/SW	HAA0909U/SW
NPT thread - Nickel plated	HAAM0304U/SW	HAAM0404U/SW	HAAM0505U/SW	HAAM0606U/SW	HAAM0707U/SW	HAAM0808U/SW	HAAM0909U/SW
NPT thread - Stainless steel	HAAS0304U/SW	HAAS0404U/SW	HAAS0505U/SW	HAAS0606U/SW	HAAS0707U/SW	HAAS0808U/SW	HAAS0909U/SW


For use with all threaded conduit including rigid





Part no. explanation HAM0304U HAM = Metric male thread

HAA = NPT male thread 0304 = Thread sizes Thread A = M16 Thread B = M20



Part no. explanation HAA0304U

HAM = Metric male thread HAA = NPT male thread 0304 = Thread sizes Thread A = %" NPT Thread B = ½" NPT

_

XP Flex couplers

Explosion-proof flexible couplings

- Corrosion-resistant ideal for washdown areas
- Flexible bronze construction with arc-resistant inner sleeve and brass fittings
- Terminated with two threaded female end fittings and male close nipples

Certification and standards












Technical specifications

½" and ¾" Hub sizes: Class I Div 1 and 2 ABCD; Class II Div 1 EFG, Class III 1" Hub Size: Class I Div 1 and 2 CD; Class II Div 1 EFG, Class III UL Listed

Dimensions





Related products



Enlargers, reducers and thread convertors pages E20–E25



Locknuts pages E28–E29



Sealing washers pages E28-E29

XP FLEX COUPLERS E19

XP Flex couplers

Explosion-proof flexible couplings

			,	Dimensions (mm)
Reference	NPT thread size (in.)	Flexible length (mm)	A	В
XPLFL16	1/2	150	39.1	36.6
XPLFL18	1/2	200	39.1	36.6
XPLFL110	1/2	250	39.1	36.6
XPLFL112	1/2	300	39.1	36.6
XPLFL115	1/2	380	39.1	36.6
XPLFL118	1/2	460	39.1	36.6
XPLFL124	1/2	610	39.1	36.6
XPLFL212	3/4	300	40.6	47.5
XPLFL215	3/4	380	40.6	47.5
XPLFL218	3/4	460	40.6	47.5
XPLFL224	3/4	610	40.6	47.5
XPLFL236	3/4	915	40.6	47.5
XPLFL318	1	460	50.08	58.7



Explosion-proof and dust-ignition-proof for use in hazardous locations

With their flexible design, ABB XP Flex couplings make it easy to achieve tight bends in conduit systems in confined spaces – or to connect stationary equipment to equipment that moves or vibrates. Their explosion-proof and corrosion-resistant construction means you can use them with confidence in hazardous and wet locations.

Convertors and accessories

Our comprehensive range of adaptors and reducers provides a method of matching threadforms on hazardous area approved equipment while ensuring the integrity and approval of the installation is maintained.

Manufactured in the UK, this range of converters meets the latest ATEX/IECEx and CSA/UL standards. This means that all the standards are marked on the product around the main body. This allows for them to be seen easily once installed, a key component of the new standard.

Metric - Technical specification

		Certification and standards	Male external thread	M16
		Connector description:	M16	_
		EX - Brass	M20	EX/M20-M16/R
	GROUP GROUP	EXN – Nickel-plated brass EXS – Stainless steel 316	M25	EX/M25-M16/R
		Certification standard:	M32	EX/M32-M16/R
	zone zone zone 22	Baseefa07 ATEX 0247X,	M40	EX/M40-M16/R
		IECEx BAS07.0090X Class I Div1 ABCD, Class II Div1 EFG	M50	EX/M50-M16/R
	CLASS DIV CLASS DIV 1	(does not include M16 and %" NPT	M63	EX/M63-M16/R
		or unplated brass products)	M75	EX/M75-M16/R
Exe (E	(Exe) (Exd)	Approved to UL	PG9	EX/PG9-M16/TC
	IP	Approved to CSA	PG11	EX/PG11-M16/TC
	- -66		PG13	EX/PG13-M16/TC
			PG16	EX/PG16-M16/TC
			PG21	EX/PG21-M16/TC
			PG29	EX/PG29-M16/TC
			PG36	EX/PG36-M16/TC
			PG42	EX/PG42-M16/TC
			PG48	EX/PG48-M16/TC
			NPT 3/8	EX/038-M16/TC
			NPT ½	EX/050-M16/TC
			NPT 3/4	EX/075-M16/TC
			NPT 1	EX/100-M16/TC
			NPT 11/4	EX/125-M16/TC
			NPT 1½	EX/150-M16/TC
			NPT 2	EX/200-M16/TC
			NPT 2½	EX/250-M16/TC
			NPT 3	EX/300-M16/TC

Enlargers (/E) are used where the thread size of the female side of the device is larger than the male side.

Reducers (/R) are used where the thread size of the female side of device is smaller than the male side.

Thread converters (/TC) are used where a conversion is required between thread types, e.g. metric to PG.

ABB enlargers, reducers and thread converters are designed for hazardous area applications and are certified to protection concepts Exd "Flameproof" and Exe "Increased Safety" for use in Zone 1, 2, 2.1, 2.2 applications. Under NEC Class I Div1 ABCD Class II Div1 EFG.

male internal thread	Metric fe					
M75	M63	M50	M40	M32	M25	M20
	-	=	=	=	EX/M16-M25/E	EX/M16-M20/E
_	-	-	-	EX/M20-M32/E	EX/M20-M25/E	-
_	-	-	EX/M25-M40/E	EX/M25-M32/E	-	EX/M25-M20/R
_	_	EX/M32-M50/E	EX/M32-M40/E	-	EX/M32-M25/R	EX/M32-M20/R
_	EX/M40-M63/E	EX/M40-M50/E	-	EX/M40-M32/R	EX/M40-M25/R	EX/M40-M20/R
EX/M50-M75/E	EX/M50-M63/E	-	EX/M50-M40/R	EX/M50-M32/R	EX/M50-M25/R	EX/M50-M20/R
EX/M63-M75/E	_	EX/M63-M50/R	EX/M63-M40/R	EX/M63-M32/R	EX/M63-M25/R	EX/M63-M20/R
<u>-</u>	EX/M75-M63/R	EX/M75-M50/R	EX/M75-M40/R	EX/M75-M32/R	EX/M75-M25/R	EX/M75-M20/R
	=	=	=	=	=	EX/PG9-M20/TC
_	_	-	-	-	_	EX/PG11-M20/TC
_	_	-	-	-	_	EX/PG13-M20/TC
_	_	-	-	-	EX/PG16-M25/TC	EX/PG16-M20/TC
_	_	-	-	EX/PG21-M32/TC	EX/PG21-M25/TC	EX/PG21-M20/TC
_	_	-	EX/PG29-M40/TC	EX/PG29-M32/TC	EX/PG29-M25/TC	EX/PG29-M20/TC
_	_	EX/PG36-M50/TC	EX/PG36-M40/TC	EX/PG36-M32/TC	EX/PG36-M25/TC	EX/PG36-M20/TC
_	EX/PG42-M63/TC	EX/PG42-M50/TC	EX/PG42-M40/TC	EX/PG42-M32/TC	EX/PG42-M25/TC	EX/PG42-M20/TC
_	EX/PG48-M63/TC	EX/PG48-M50/TC	EX/PG48-M40/TC	EX/PG48-M32/TC	EX/PG48-M25/TC	EX/PG48-M20/TC
	-	_	_	_	_	_
_	_	_	-	_	EX/050-M25/TC	EX/050-M20/TC
_	_	_	_	EX/075-M32/TC	EX/075-M25/TC	EX/075-M20/TC
_	_	_	EX/100-M40/TC	EX/100-M32/TC	EX/100-M25/TC	EX/100-M20/TC
_	_	EX/125-M50/TC	EX/125-M40/TC	EX/125-M32/TC	EX/125-M25/TC	EX/125-M20/TC
_	EX/150-M63/TC	EX/150-M50/TC	EX/150-M40/TC	EX/150-M32/TC	EX/150-M25/TC	EX/150-M20/TC
_	EX/200-M63/TC	EX/200-M50/TC	EX/200-M40/TC	EX/200-M32/TC	EX/200-M25/TC	EX/200-M20/TC
_	_	EX/250-M50/TC	EX/250-M40/TC	EX/250-M32/TC	EX/250-M25/TC	EX/250-M20/TC
EX/300-M75/TC	_	EX/300-M50/TC	EX/300-M40/TC	EX/300-M32/TC	EX/300-M25/TC	EX/300-M20/TC

NPT – Technical specification

		Certification and standards	Male external thread	NPT 3/8	NPT ⅓
		Connector description:	M16	EX/M16-038/TC	EX/M16-050/TC
		EX – Brass	M20	-	EX/M20-050/TC
GROUP		EXN – Nickel-plated brass EXS – Stainless steel 316	M25	_	EX/M25-050/TC
		Certification standard:	M32	_	EX/M32-050/TC
	zone zone zone 22	Baseefa07 ATEX 0247X,	M40	_	EX/M40-050/TC
		IECEx BAS07.0090X Class I Div1 ABCD, Class II Div1 EFG	M50	-	EX/M50-050/TC
	CLASS DIV CLASS DIV	(does not include M16 and %" NPT or unplated brass products) Approved to UL Approved to CSA	M63	-	EX/M63-050/TC
	Exe (Exa) or un		M75		EX/M75-050/TC
			PG9	_	EX/PG9-050/TC
	IP ₆₆		PG11	_	EX/PG11-050/TC
	<u>66</u>		PG13	-	EX/PG13-050/TC
			PG16	-	EX/PG16-050/TC
			PG21	-	EX/PG21-050/TC
			PG29	-	EX/PG29-050/TC
			PG36	-	EX/PG36-050/TC
			PG42	-	EX/PG42-050/TC
			PG48	_	EX/PG48-050/TC
			NPT ½	-	
			NPT ¾	-	EX/075-050/R
			NPT 1	-	EX/100-050/R
			NPT 11/4	_	EX/125-050/R
			NPT 11/2	-	EX/150-050/R
			NPT 2	-	EX/200-050/R
•	r	NPT 21/2	-	EX/250-050/R	
			NPT 3		EX/300-050/R

le internal thread	NPT fema					
NPT 3	NPT 2⅓	NPT 2	NPT 1½	NPT 11/4	NPT 1	NPT ¾
=	_	-	_	=	_	-
-	_	-	_	_	_	EX/M20-075/TC
-	_	-	_	_	EX/M25-100/TC	EX/M25-075/TC
-	_	-	_	EX/M32-125/TC	EX/M32-100/TC	EX/M32-075/TC
-	_	-	EX/M40-150/TC	EX/M40-125/TC	EX/M40-100/TC	EX/M40-075/TC
-	_	EX/M50-200/TC	EX/M50-150/TC	EX/M50-125/TC	EX/M50-100/TC	EX/M50-075/TC
-	_	EX/M63-200/TC	EX/M63-150/TC	EX/M63-125/TC	EX/M63-100/TC	EX/M63-075/TC
-	_	EX/M75-200/TC	EX/M75-150/TC	EX/M75-125/TC	EX/M75-100/TC	EX/M75-075/TC
=	_	-	_	=	_	-
-	-	-	-	=	_	-
-	-	-	-	=	_	-
-	-	-	-	=	_	EX/PG16-075/TC
_	-	-	-	=	EX/PG21-100/TC	EX/PG21-075/TC
-	-	-	EX/PG29-150/TC	EX/PG29-125/TC	EX/PG29-100/TC	EX/PG29-075/TC
-	-	-	EX/PG36-150/TC	EX/PG36-125/TC	EX/PG36-100/TC	EX/PG36-075/TC
-	-	EX/PG42-200/TC	EX/PG42-150/TC	EX/PG42-125/TC	EX/PG42-100/TC	EX/PG42-075/TC
-	-	EX/PG48-200/TC	EX/PG48-150/TC	EX/PG48-125/TC	EX/PG48-100/TC	EX/PG48-075/TC
=	=	-	=	=	=	EX/050-075/E
-	-	-	-	-	EX/075-100/E	-
-	-	-	-	EX/100-125/E	-	EX/100-075/R
-	-	-	EX/125-150/E	-	EX/125-100/R	EX/125-075/R
_	-	EX/150-200/E	-	EX/150-125/R	EX/150-100/R	EX/150-075/R
_	-	-	EX/200-150/R	EX/200-125/R	EX/200-100/R	EX/200-075/R
EX/250-300/E	-	EX/250-200/R	EX/250-150/R	EX/250-125/R	EX/250-100/R	EX/250-075/R
_	EX/300-250/R	EX/300-200/R	EX/300-150/R	EX/300-125/R	EX/300-100/R	EX/300-075/R

PG - Technical specification

			Male external		
		Certification and standards	thread	PG9	PG11
		Connector description:	M16	EX/M16-PG9/TC	EX/M16-PG11/TC
		EX – Brass	M20	EX/M20-PG9/TC	EX/M20-PG11/TC
	GROUP GROUP	EXN – Nickel-plated brass EXS – Stainless steel 316	M25	EX/M25-PG9/TC	EX/M25-PG11/TC
		Certification standard:	M32	EX/M32-PG9/TC	EX/M32-PG11/TC
	zone zone zone 22	Baseefa07 ATEX 0247X,	M40	EX/M40-PG9/TC	EX/M40-PG11/TC
		IECEX BASO7.0090X	M50	EX/M50-PG9/TC	EX/M50-PG11/TC
	CLASS DIV CLASS DIV 1	Class I Div1 ABCD, Class II Div1 EFG (does not include M16 and %" NPT	M63	EX/M63-PG9/TC	EX/M63-PG11/TC
	<u> </u>	or unplated brass products)	M75	EX/M75-PG9/TC	EX/M75-PG11/TC
	(Exe) (Exa)	Approved to UL	PG11	EX/PG11-PG9/R	-
	IP	Approved to CSA	PG13	EX/PG13-PG9/R	EX/PG13-PG11/R
	IP ₆₆		PG16	EX/PG16-PG9/R	EX/PG16-PG11/R
			PG21	EX/PG21-PG9/R	EX/PG21-PG11/R
			PG29	EX/PG29-PG9/R	EX/PG29-PG11/R
			PG36	EX/PG36-PG9/R	EX/PG36-PG11/R
			PG42	EX/PG42-PG9/R	EX/PG42-PG11/R
			PG48	EX/PG48-PG9/R	EX/PG48-PG11/R
			NPT ½	EX/050-PG9/TC	EX/050-PG11/TC
			NPT ¾	EX/075-PG9/TC	EX/075-PG11/TC
			NPT 1	EX/100-PG9/TC	EX/100-PG11/TC
			NPT 1¼	EX/125-PG9/TC	EX/125-PG11/TC
			NPT 1½	EX/150-PG9/TC	EX/150-PG11/TC
			NPT 2	EX/200-PG9/TC	EX/200-PG11/TC

male internal threa	PG fe					
PG4	PG42	PG36	PG29	PG21	PG16	PG13
	-	_	_	_	-	EX/M16-PG13/TC
	-	-	-	-	EX/M20-PG16/TC	EX/M20-PG13/TC
	-	-	-	EX/M25-PG21/TC	EX/M25-PG16/TC	EX/M25-PG13/TC
	_	_	EX/M32-PG29/TC	EX/M32-PG21/TC	EX/M32-PG16/TC	EX/M32-PG13/TC
	_	EX/M40-PG36/TC	EX/M40-PG29/TC	EX/M40-PG21/TC	EX/M40-PG16/TC	EX/M40-PG13/TC
	EX/M50-PG42/TC	EX/M50-PG36/TC	EX/M50-PG29/TC	EX/M50-PG21/TC	EX/M50-PG16/TC	EX/M50-PG13/TC
EX/M63-PG48/T	EX/M63-PG42/TC	EX/M63-PG36/TC	EX/M63-PG29/TC	EX/M63-PG21/TC	EX/M63-PG16/TC	EX/M63-PG13/TC
EX/M75-PG48/T	EX/M75-PG42/TC	EX/M75-PG36/TC	EX/M75-PG29/TC	EX/M75-PG21/TC	EX/M75-PG16/TC	EX/M75-PG13/TC
	-	=	=	=	=	_
	-	-	-	-	-	-
	-	-	-	EX/P16-PG21/E	-	EX/PG16-PG13/R
	-	-	EX/PG21-PG29/E	-	EX/PG21-PG16/R	EX/PG21-PG13/R
		EX/PG29-PG36/E	-	EX/PG29-PG21/R	EX/PG29-PG16/R	EX/PG29-PG13/R
	EX/PG36-PG48/E	-	EX/PG36-PG29/R	EX/PG36-PG21/R	EX/PG36-PG16/R	EX/PG36-PG13/R
EX/PG42-PG48/	-	EX/PG42-PG36/R	EX/PG42-PG29/R	EX/PG42-PG21/R	EX/PG42-PG16/R	EX/PG42-PG13/R
	EX/PG48-PG42/R	EX/PG48-PG36/R	EX/PG48-PG29/R	EX/PG48-PG21/R	EX/PG48-PG16/R	EX/PG48-PG13/R
	=	=	=	=	EX/050-PG16/TC	EX/050-PG13/TC
	-	-	-	EX/075-PG21/TC	EX/075-PG16/TC	EX/075-PG13/TC
	-	-	EX/100-PG29/TC	EX/100-PG21/TC	EX/100-PG16/TC	EX/100-PG13/TC
	-	EX/125-PG36/TC	EX/125-PG29/TC	EX/125-PG21/TC	EX/125-PG16/TC	EX/125-PG13/TC
	EX/150-PG42/TC	EX/150-PG36/TC	EX/150-PG29/TC	EX/150-PG21/TC	EX/150-PG16/TC	EX/150-PG13/TC
EX/200-PG48/T	EX/200-PG42/TC	EX/200-PG36/TC	EX/200-PG29/TC	EX/200-PG21/TC	EX/200-PG16/TC	EX/200-PG13/TC

Stopping plugs

Certification and characteristics

For use in potentially explosive atmospheres. Manufactured from brass, nickel-plated brass or stainless steel.

Standard Exd stopping plug



For nickel-plated brass, add the letter N after the EX prefix and for stainless steel, add the letter S after the EX prefix, e.g. EXS/M16/SP Does not include M16 and % in. NPT or unplated brass products

Tamperproof Exd stopping plug - Group I and II, Zones 1, 2, 21 and 22, Class I DIv 1 ABCD, Class II Div 1 EFG

	(C) (D) INCOLU	Certification standard:	NF	T thread size (inch)	3/8	
		Baseefa 08 ATEX 6324 IECEx BAS08.0109X	Met	ric thread size (mm)	20	
	GROUP GROUP	Exd I and Exd IIC	Туре	PG thread size	PG9	
	ZONE ZONE ZONE 22 ZONE 22	UL listed (nickel-plated brass	NPT thread	NPT thread – Brass		
		and stainless steel only) Class I Div 1 ABCD	Metric - Bra	ass	EX/M16/TSP	
	CLASS DIV CLASS II 1	Class II Div 1 EFG	PG thread – Brass (EX)		EX/PG9/TSP	
•	(Exc) P ₆₆					

 $For nickel-plated \ brass, add \ the \ letter \ Nafter \ the \ EX \ prefix \ and \ for \ stainless \ steel, add \ the \ letter \ Safter \ the \ EX \ prefix, e.g. \ EXS/M16/SP$ Does not include M16 and % in. NPT or unplated brass products

Hex head Exe stopping plug - Group I and II, Zones 1, 2, 21 and 22, Class I DIv 1 ABCD, Class II Div 1 EFG



Temperature: -60 °C to +80 °C

For nickel-plated brass, add the letter N after the EX prefix and for stainless steel, add the letter S after the EX prefix, e.g. EXS/M16/SP Does not include M16 and % in. NPT or unplated brass products

Dome head Exe stopping plug - Group I and II, Zones 1, 2, 21 and 22, Class I DIv 1 ABCD, Class II Div 1 EFG



For nickel-plated brass, add the letter N after the EX prefix and for stainless steel, add the letter S after the EX prefix, e.g. EXS/M16/SP Products supplied with sealing washers and O-rings Does not include M16 and % in. NPT or unplated brass products

STOPPING PLUGS E27

Stopping plugs

Technical specifications

		2	11/2	11/4	1	3/4	⅓2
		63	50	40	32	25	20
PG48	PG42	PG36	PG29	PG21	PG16	PG13	PG11
_	-	EX/200/SP	EX/150/SP	EX/125/SP	EX/100/SP	EX/075/SP	EX/050/SP
_	_	EX/M63/SP	EX/M50/SP	EX/M40/SP	EX/M32/SP	EX/M25/SP	EX/M20/SP
EX/PG48/SP	EX/PG42/SP	EX/PG36/SP	EX/PG29/SP	EX/PG21/SP	EX/PG16/SP	EX/PG13/SP	EX/PG11/SP

		2	11/2	11/4	1	3/4	1/2
		63	50	40	32	25	20
PG48	PG42	PG36	PG29	PG21	PG16	PG13	PG11
	-	EX/200/TSP	EX/150/TSP	EX/125/TSP	EX/100/TSP	EX/075/TSP	EX/050/TSP
_	-	EX/M63/TSP	EX/M50/TSP	EX/M40/TSP	EX/M32/TSP	EX/M25/TSP	EX/M20/TSP
EX/PG48/TSP	EX/PG42/TSP	EX/PG36/TSP	EX/PG29/TSP	EX/PG21/TSP	EX/PG16/TSP	EX/PG13/TSP	EX/PG11/TSP

,	1/2	3/4	1	11/4	11/2	2		
	20	25	32	40	50	63		
	PG11	PG13	PG16	PG21	PG29	PG36	PG42	PG48
	EX/M20/HSP	EX/M25/HSP	EX/M32/HSP	EX/M40/HSP	EX/M50/HSP	EX/M63/HSP	-	_
	EX/PG11/HSP	EX/PG13/HSP	EX/PG16/HSP	EX/PG21/HSP	EX/PG29/HSP	EX/PG36/HSP	EX/PG42/HSP	EX/PG48/HSP

		2	11/2	11/4	1	3/4	1/2	
		63	50	40	32	25	20	
PG48	PG42	PG36	PG29	PG21	PG16	PG13	PG11	
	_	EX/M63/DSP	EX/M50/DSP	EX/M40/DSP	EX/M32/DSP	EX/M25/DSP	EX/M20/DSP	
EX/PG48/DSP	EX/PG42/DSP	EX/PG36/DSP	EX/PG29/DSP	EX/PG21/DSP	EX/PG16/DSP	EX/PG13/DSP	EX/PG11/DSP	

_

Couplers, sealing washers and locknuts

Certification and characteristics

Couplers, sealing washers and locknuts

For use in potentially explosive atmospheres. Manufactured from either brass, nickel-plated brass, stainless steel or nylon and fiber.

Coupler - Female to female thread couplers for use in both Exd and Exe applications









Certification standard: Baseefa 08 ATEX 0359U IECEx BAS08.0121U

Temperature: -60 °C to +200 °C

Hex locknut - For metric threads and NPT threads (nickel-plated brass only)



Sealing joint washer – For use with all ATEX and IECEx approved products (nylon only)



Certification standard: Nylon metric approved for use with all ATEX/IECEx products

Earth tag – To be used to create an earthing bond on an enclosure, when a cable gland is used



Couplers, sealing washers and locknuts

Technical specifications

See	Metric thread size (mm)	16	20	25	32	40	50	63	75
note 1 Type	PG thread size	3/8	1/2	3/4	1	11/4	1 1/2	2	2½
Metric -	Brass	EX/M16/C	EX/M20/C	EX/M25/C	EX/M32/C	EX/M40/C	EX/M50/C	EX/M63/C	EX/M75/C
NPT thre	ead – Brass	EX/038/C	EX/050/C	EX/075/C	EX/100/C	EX/125/C	EX/150/C	EX/200/C	EX/250/P

For nickel plated brass, add the letter N after the EX prefix and for stainless steel, add the letter S after the EX prefix, e.g. EXS/M16/C Does not include M16 and % NPT or unplated brass products

See	Metric thread size (mm)	16	20	25	32	40	50	63	75
note 1 Type	PG thread size	3/8	1/2	3/4	1	11/4	11/2	2	21/2
Metric –	Stainless steel	_	MXWH04	MXWH05	MXWH06	MXWH07	MXWH08	_	
Metric –	Brass	WHMB03	WHMB04	WHMB05	WHMB06	WHMB07	WHMB08	-	_
Metric –	Nickel-plated brass	WHMM03	WHMM04	WHMM05	WHMM06	WHMM07	WHMM08	WHMM09	_
NPT thre	ad – Nickel-plated brass	_	WHAM04	WHAM05	WHAM06	WHAM07	WHAM08	WHAM09	_


	Metric thread size (mm)	16	20	25	32	40	50	63	75
_	PG thread size	3/8	1/2	3/4	1	11/4	1½	2	21/2
See note 1	Outside diameter (mm)	22	26	34.3	41.5	52	66.5	84.5	_
Type	Thickness (mm)	1.6	1.6	1.7	1.7	2	2	2	_
Metric – (ATEX/IE	Nylon ECEx approved)	EXFM03	EXFM04	EXFM05	EXFM05	EXFM07	EXFM08	EXFM09	_
Metric –	Fiber	EXFM03F	EXFM04F	EXFM05F	EXFM05F	EXFM07F	EXFM08F	-	_

See	Metric thread size (mm)	16	20	25	32	40	50	63	75
note 1 Type	PG thread size	3/8	1/2	3/4	1	11/4	1½	2	21/2

Earth tag - Brass

EX/M16/TAG EX/M20/TAG EX/M25/TAG EX/M32/TAG EX/M40/TAG EX/M53/TAG EX/M63/TAG EX/M75/TAG

Ex standards worldwide



Key of symbols

Product approvals















IECEx

INMETRO

INTERTEK

Product characteristics





























Type Exd













